



Illuminable selector switch, 30 mm, round, Metal matte, black, Selector switch short, front ring for flush installation, latching, actuating angle 2x45°, 10:30h/12h/13:30h

|                                                    |                                        |
|----------------------------------------------------|----------------------------------------|
| product brand name                                 | SIRIUS ACT                             |
| product designation                                | Selector switches                      |
| design of the product                              | Actuating/signaling element            |
| product type designation                           | 3SU1                                   |
| product line                                       | Metal, matt, flat, 30 mm               |
| <b>Enclosure</b>                                   |                                        |
| number of command points                           | 1                                      |
| <b>Actuator</b>                                    |                                        |
| design of the actuating element                    | Selector, short                        |
| principle of operation of the actuating element    | latching, 2x45° (10:30 h/12 h/13:30 h) |
| product extension optional                         |                                        |
| • light source                                     | Yes                                    |
| • contact module                                   | Yes                                    |
| color of the actuating element                     | black                                  |
| material of the actuating element                  | plastic                                |
| shape of the actuating element                     | Handle                                 |
| outer diameter of the actuating element            | 38 mm                                  |
| number of switching positions                      | 3                                      |
| actuating angle                                    |                                        |
| • clockwise                                        | 45°                                    |
| • anticlockwise                                    | 45°                                    |
| <b>Front ring</b>                                  |                                        |
| product component front ring                       | Yes                                    |
| design of the front ring                           | Flat                                   |
| material of the front ring                         | Metal, matt                            |
| color of the front ring                            | sand gray                              |
| <b>General technical data</b>                      |                                        |
| protection class IP                                | IP66, IP67, IP69(IP69K)                |
| degree of protection NEMA rating                   | 1, 2, 3, 3R, 4, 4X, 12, 13             |
| shock resistance                                   |                                        |
| • according to IEC 60068-2-27                      | sinusoidal half-wave 15g / 11 ms       |
| • for railway applications according to EN 61373   | Category 1, Class B                    |
| vibration resistance                               |                                        |
| • according to IEC 60068-2-6                       | 10 ... 500 Hz: 5g                      |
| • for railway applications according to EN 61373   | Category 1, Class B                    |
| operating frequency maximum                        | 1 800 1/h                              |
| mechanical service life (operating cycles) typical | 300 000                                |
| reference code according to IEC 81346-2            | S                                      |
| Substance Prohibitance (Date)                      | 03/01/2017                             |
| Weight                                             | 71 g                                   |

| Safety related data                                                                 |         |
|-------------------------------------------------------------------------------------|---------|
| <b>proportion of dangerous failures</b>                                             |         |
| • with low demand rate according to SN 31920                                        | 20 %    |
| • with high demand rate per NC contact according to SN 31920                        | 20 %    |
| • with high demand rate per NO contact according to SN 31920                        | 50 %    |
| <b>B10 value with high demand rate according to SN 31920</b>                        | 300 000 |
| <b>failure rate [FIT] with low demand rate per NC contact according to SN 31920</b> | 100 FIT |
| IEC 61508                                                                           |         |
| T1 value for proof test interval or service life according to IEC 61508             | 20 a    |

| Ambient conditions                                             |                                                                    |
|----------------------------------------------------------------|--------------------------------------------------------------------|
| <b>ambient temperature</b>                                     |                                                                    |
| • during operation                                             | -25 ... +70 °C                                                     |
| • during storage                                               | -40 ... +80 °C                                                     |
| environmental category during operation according to IEC 60721 | 3M6, 3S2, 3B2, 3C3, 3K6 (with relative air humidity of 10 ... 95%) |

| Installation/ mounting/ dimensions                 |         |
|----------------------------------------------------|---------|
| <b>height</b>                                      | 44.8 mm |
| <b>width</b>                                       | 38 mm   |
| <b>shape of the installation opening</b>           | round   |
| <b>mounting diameter</b>                           | 30.5 mm |
| <b>positive tolerance of installation diameter</b> | 0.5 mm  |
| <b>mounting height</b>                             | 22.1 mm |
| <b>installation width</b>                          | 38 mm   |
| <b>installation depth</b>                          | 32.1 mm |

| Approvals Certificates          |                          |
|---------------------------------|--------------------------|
| <b>General Product Approval</b> | <b>Test Certificates</b> |



[Type Test Certificates/Test Report](#)

[Special Test Certificate](#)

|                             |                     |                                                                             |
|-----------------------------|---------------------|-----------------------------------------------------------------------------|
| <b>Maritime application</b> | <b>other</b>        | <b>Environment</b>                                                          |
| <br>LRS                     | <br>PRS             | <br>RINA                                                                    |
|                             | <br>产品合格<br>QC PASS | <a href="#">Confirmation</a><br><a href="#">Environmental Confirmations</a> |

#### Further information

##### Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

##### Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

##### Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

##### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1062-2DL10-0AA0>

##### Cax online generator


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU1062-2DL10-0AA0>

##### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3SU1062-2DL10-0AA0>

##### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3SU1062-2DL10-0AA0&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1062-2DL10-0AA0&lang=en)



---

last modified:

5/21/2025 