



Key-operated switch IKON, 22 mm, round, metal, shiny, lock number 360012K1, with 2 keys, 3 switch positions I-O-II, latching, actuating angle 2x45°, 10:30h/12h/13:30h, Key removal I+O+II, Z=50-unit packaging

|                                                    |                                        |
|----------------------------------------------------|----------------------------------------|
| product brand name                                 | SIRIUS ACT                             |
| product designation                                | Key-operated switches                  |
| design of the product                              | Actuating/signaling element            |
| product type designation                           | 3SU1                                   |
| product line                                       | Metal, shiny, 22 mm                    |
| manufacturer's article number of included key      | <a href="#">3SU1950-0FR80-0AA0</a>     |
| <b>Actuator</b>                                    |                                        |
| principle of operation of the actuating element    | latching, 2x45° (10:30 h/12 h/13:30 h) |
| product extension optional light source            | No                                     |
| color                                              |                                        |
| • of the actuating element                         | silver                                 |
| material of the actuating element                  | metal                                  |
| shape of the actuating element                     | Key                                    |
| outer diameter of the actuating element            | 29.5 mm                                |
| number of switching positions                      | 3                                      |
| switch position for key distraction                | O+I+II                                 |
| actuating angle                                    |                                        |
| • clockwise                                        | 45°                                    |
| • anticlockwise                                    | 45°                                    |
| lock make                                          | ICON                                   |
| key number                                         | 360012K1                               |
| <b>Front ring</b>                                  |                                        |
| product component front ring                       | Yes                                    |
| design of the front ring                           | Standard                               |
| material of the front ring                         | Metal, high gloss                      |
| color of the front ring                            | silver                                 |
| <b>General technical data</b>                      |                                        |
| protection class IP                                | IP66, IP67, IP69(IP69K)                |
| protection class IP of the terminal                | IP20                                   |
| degree of protection NEMA rating                   | 1, 2, 3, 3R, 4, 4X, 12, 13             |
| shock resistance                                   |                                        |
| • according to IEC 60068-2-27                      | sinusoidal half-wave 15g / 11 ms       |
| vibration resistance                               |                                        |
| • according to IEC 60068-2-6                       | 10 ... 500 Hz: 5g                      |
| operating frequency maximum                        | 1 800 1/h                              |
| mechanical service life (operating cycles) typical | 300 000                                |
| reference code according to IEC 81346-2            | S                                      |
| Substance Prohibitance (Date)                      | 10/01/2014                             |
| Net Weight                                         | 0.146 kg                               |

| Ambient conditions                                             |                                                                    |
|----------------------------------------------------------------|--------------------------------------------------------------------|
| <b>ambient temperature</b>                                     |                                                                    |
| • during operation                                             | -25 ... +70 °C                                                     |
| • during storage                                               | -40 ... +80 °C                                                     |
| environmental category during operation according to IEC 60721 | 3M6, 3S2, 3B2, 3C3, 3K6 (with relative air humidity of 10 ... 95%) |

| Environmental footprint                                |                 |
|--------------------------------------------------------|-----------------|
| Environmental Product Declaration(EPD)                 | Yes             |
| global warming potential [CO2 eq] total                | 0.593 kg        |
| global warming potential [CO2 eq] during manufacturing | 0.625 kg        |
| global warming potential [CO2 eq] during operation     | 0.235 kg        |
| global warming potential [CO2 eq] after end of life    | -0.267 kg       |
| Siemens Eco Profile (SEP)                              | Siemens EcoTech |

| Installation/ mounting/ dimensions          |         |
|---------------------------------------------|---------|
| height                                      | 29.5 mm |
| width                                       | 29.5 mm |
| shape of the installation opening           | round   |
| mounting diameter                           | 22.3 mm |
| positive tolerance of installation diameter | 0.4 mm  |
| mounting height                             | 56.2 mm |
| installation width                          | 29.5 mm |
| installation depth                          | 25.4 mm |

| Approvals Certificates   |                   |
|--------------------------|-------------------|
| General Product Approval | Test Certificates |



[Type Test Certificates/Test Report](#)

[Special Test Certificate](#)

|                      |       |
|----------------------|-------|
| Maritime application | other |
|----------------------|-------|



[Confirmation](#)



| Environment |
|-------------|
|-------------|



Siemens  
EcoTech



[Environmental Confirmations](#)

| Further information |
|---------------------|
|---------------------|

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1050-5XL11-0AA0-Z X90>

Cax online generator


<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU1050-5XL11-0AA0-Z X90>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3SU1050-5XL11-0AA0-Z X90>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[https://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3SU1050-5XL11-0AA0-Z X90&lang=en](https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1050-5XL11-0AA0-Z X90&lang=en)



---

last modified:

4/1/2025 