



Figure similar

!!! product phase-out !!! the preferred successor is 3UG5501-1AW30 analog monitoring relay level monitoring resistance monitoring from 2 to 200 kohm overshoot and undershoot 24 to 240 V AC/DC 50 to 60 Hz DC and AC 2-step or 1-step control tripping delay 0.5 to 10 s 1 changeover contact screw terminal


product brand name	SIRIUS
product designation	Level monitoring relay with analog setting
product type designation	3UG4
manufacturer's article number of the optional sensor	2-pole and 3-pole sensors 3UG3207
General technical data	
product function	Monitoring relay for level monitoring
display version LED	Yes
<ul style="list-style-type: none">• Apparent power consumption at DC<ul style="list-style-type: none">— at 24 V maximum— at 240 V maximum• apparent power consumption at AC<ul style="list-style-type: none">— at 24 V maximum— at 240 V maximum	2 VA 4 VA 2 VA 4 VA
insulation voltage <ul style="list-style-type: none">• for overvoltage category III according to IEC 60664 with degree of pollution 3 rated value	300 V
degree of pollution	3
type of voltage <ul style="list-style-type: none">• of the operating voltage for actuation• of the control supply voltage	AC/DC AC/DC
surge voltage resistance rated value	4 kV
shock resistance according to IEC 60068-2-27	sinusoidal half-wave 15g / 11 ms
vibration resistance according to IEC 60068-2-6	1 ... 6 Hz: 15 mm, 6 ... 500 Hz: 2g
mechanical service life (operating cycles) typical	10 000 000
electrical endurance (operating cycles) at AC-15 at 230 V typical	100 000
reference code according to IEC 81346-2	K
relative repeat accuracy	1 %
Substance Prohibitance (Date)	05/01/2012
SVHC substance name	Lead - 7439-92-1 Lead monoxide (lead oxide) - 1317-36-8 6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol - 119-47-1
Net Weight	0.144 kg
Product Function	
product function <ul style="list-style-type: none">• outlet monitoring adjustable• adjustable responsiveness• inlet monitoring adjustable• external reset	Yes Yes Yes Yes

Control circuit/ Control	
control supply voltage at AC	
• at 50 Hz rated value	24 ... 240 V
• at 60 Hz rated value	24 ... 240 V
control supply voltage at DC rated value	24 ... 240 V
operating range factor control supply voltage rated value at DC	
• initial value	0.85
• full-scale value	1.1
operating range factor control supply voltage rated value at AC at 50 Hz	
• initial value	0.85
• full-scale value	1.1
operating range factor control supply voltage rated value at AC at 60 Hz	
• initial value	0.85
• full-scale value	1.1
Measuring circuit	
adjustable response delay time	
• when starting	0.5 ... 10 s
• with lower or upper limit violation	0.5 ... 10 s
buffering time in the event of power failure minimum	200 ms
response time maximum	300 ms
physical measuring principle	conductive
Precision	
relative metering precision	20 %
temperature drift per °C	1 %/°C
Auxiliary circuit	
number of NC contacts delayed switching	0
number of NO contacts delayed switching	0
number of CO contacts	
• delayed switching	1
operating frequency with 3RT2 contactor maximum	5 000 1/h
ampacity of the output relay at AC-15	
• at 250 V at 50/60 Hz	3 A
• at 400 V at 50/60 Hz	3 A
ampacity of the output relay at DC-13	
• at 24 V	1 A
• at 125 V	0.2 A
• at 250 V	0.1 A
operational current at 17 V minimum	5 mA
continuous current of the DIAZED fuse link of the output relay	4 A
Electromagnetic compatibility	
conducted interference	
• due to burst according to IEC 61000-4-4	2 kV
• due to conductor-earth surge according to IEC 61000-4-5	2 kV
• due to conductor-conductor surge according to IEC 61000-4-5	1 kV
field-based interference according to IEC 61000-4-3	10 V/m
electrostatic discharge according to IEC 61000-4-2	6 kV contact discharge / 8 kV air discharge
Galvanic isolation	
galvanic isolation	
• between input and output	Yes
• between the outputs	No
Electrical Safety	
protection class IP on the front according to IEC 60529	IP20
Connections/ Terminals	
product component removable terminal for auxiliary and control circuit	Yes

type of electrical connection	screw terminal		
type of connectable conductor cross-sections <ul style="list-style-type: none"> • solid • finely stranded with core end processing • for AWG cables solid • for AWG cables stranded 	1x (0.5 ... 4 mm ²), 2x (0.5 ... 2.5 mm ²) 1x (0.5 ... 2.5 mm ²), 2x (0.5 ... 1.5 mm ²) 2x (20 ... 14) 2x (20 ... 14)		
connectable conductor cross-section <ul style="list-style-type: none"> • solid • finely stranded with core end processing 	0.5 ... 4 mm ² 0.5 ... 2.5 mm ²		
AWG number as coded connectable conductor cross section <ul style="list-style-type: none"> • solid • stranded 	20 ... 14 20 ... 14		
tightening torque with screw-type terminals	0.8 ... 1.2 N·m		
Installation/ mounting/ dimensions			
mounting position	any		
fastening method	screw and snap-on mounting		
height	92 mm		
width	22.5 mm		
depth	91 mm		
required spacing <ul style="list-style-type: none"> • with side-by-side mounting <ul style="list-style-type: none"> — forwards — backwards — upwards — downwards — at the side • for grounded parts <ul style="list-style-type: none"> — forwards — backwards — upwards — at the side — downwards • for live parts <ul style="list-style-type: none"> — forwards — backwards — upwards — downwards — at the side 	0 mm 0 mm 0 mm 0 mm 0 mm 0 mm 0 mm 0 mm 0 mm 0 mm 0 mm 0 mm 0 mm 0 mm 0 mm		
Ambient conditions			
installation altitude at height above sea level maximum	2 000 m		
ambient temperature <ul style="list-style-type: none"> • during operation • during storage • during transport 	-25 ... +60 °C -40 ... +80 °C -40 ... +80 °C		
Environmental footprint			
Environmental Product Declaration (EPD)	Yes		
global warming potential [CO ₂ eq] total	16.1 kg		
global warming potential [CO ₂ eq] during manufacturing	3.51 kg		
global warming potential [CO ₂ eq] during operation	13.7 kg		
global warming potential [CO ₂ eq] after end of life	-1.12 kg		
Approvals Certificates			
<table> <tr> <td>General Product Approval</td><td>EMV</td></tr> </table>		General Product Approval	EMV
General Product Approval	EMV		



EMV	Test Certificates	Maritime application	other
KC	Special Test Certificate	Type Test Certificates/Test Report	  

other	Railway	Environment
Confirmation	Special Test Certificate	Environmental Confirmations
		

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3UG4501-1AW30>

Cax online generator


<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3UG4501-1AW30>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3UG4501-1AW30>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3UG4501-1AW30&lang=en



last modified:

10/17/2025 