

SITOP UPS1100/Battery module/24V/2.5AH

SITOP UPS1100 battery module with maintenance- free sealed pure lead-acid for SITOP DC UPS modules 24 V DC 2.5 Ah



Technical Product Detail Page

<https://i.siemens.com/1P6EP4132-0GB00-0AY0>

electrical data

end-of-charge voltage at DC

• at -10 °C recommended	28 V
• at 0 °C recommended	28 V
• at 10 °C recommended	27.8 V
• at 20 °C recommended	27.3 V
• at 30 °C recommended	26.8 V
• at 40 °C recommended	26.6 V
• at 50 °C recommended	26.3 V
• at 60 °C recommended	26 V

output

battery capacity	2.5 A-h
output current rated value	20 A
output current in buffering mode maximum	20 A
peak current	60 A; for 30 ms
charging current maximum	5 A
output voltage at DC rated value	24 V

interfaces

communication function	Yes
------------------------	-----

protection and monitoring

design of short-circuit protection	Battery fuse 25 A/32 V (solid-state circuitry blade-type fuse + support)
design of the overload protection	Valve control
display version for normal operation	LED green: Battery OK; LED flashing green: Error or warning; OFF: No communication

safety

operating resource protection class	Class III
protection class IP	IP20

standards, specifications, approvals

certificate of suitability	
• CE marking	Yes
• UL approval	Yes; cURus-Recognized (UL 1778, CSA C22.2 No. 107.1), File E219627
• EAC approval	Yes

standards, specifications, approvals hazardous environments

certificate of suitability	
• ATEX	No

standards, specifications, approvals marine classification

shipbuilding approval	Yes
Marine classification association	


<ul style="list-style-type: none"> American Bureau of Shipping Europe Ltd. (ABS) Det Norske Veritas (DNV) 	Yes Yes
standards, specifications, approvals Environmental Product Declaration	
Environmental Product Declaration	Yes
global warming potential [CO ₂ eq]	
<ul style="list-style-type: none"> total during manufacturing during operation after end of life 	13.68 kg 9.127 kg 2.917 kg 0.481 kg
ambient conditions	
ambient condition	For storage, mounting and operation of lead-acid batteries, the relevant DIN/VDE regulations or country-specific regulations (e.g. VDE 0510 Part 2/EN 50272-2) must be observed. You must ensure that the battery site is sufficiently ventilated. Possible sources of ignition must be at least 50 cm away.
ambient temperature	
<ul style="list-style-type: none"> during operation during transport during storage 	-40 ... +60 °C -40 ... +60 °C -40 ... +60 °C
relative temporary capacity loss at 20 °C in a month typical	3 %
service life	
service life of energy storage	
<ul style="list-style-type: none"> typical at 20 °C typical at 30 °C typical at 40 °C typical at 50 °C typical at 60 °C typical 	capacity falls to 80 % of original capacity (according to EUROBAT) 10 a 7 a 3 a 1.5 a 1 a
note	Along with the storage and operating temperature, other factors such as the duration of the storage period and the charge status during storage have a decisive influence on the possible useful life. Batteries should therefore be stored as briefly as possible, always fully charged, and within the temperature range 0 to +20 °C.
connection method	
type of electrical connection	screw terminal
<ul style="list-style-type: none"> for UPS module for control circuit and status message 	1 screw terminal each for 0.2 ... 6 mm ² for + BAT and - BAT 1 screw terminal each for 0.14 ... 4 mm ²
mechanical data	
width × height × depth of the enclosure	265 × 115 × 76 mm
installation width × mounting height	265 mm × 130 mm
required spacing	
<ul style="list-style-type: none"> top bottom left right 	15 mm 0 mm 0 mm 0 mm
fastening method	snaps onto DIN rail EN 60715 35x7.5/15 or keyhole mounting for hooking in to M4 screws
<ul style="list-style-type: none"> DIN-rail mounting S7 rail mounting wall mounting 	Yes No Yes
net weight	3.7 kg
number of cells	12
accessories	
product component included	Accessories pack with solid-state circuitry fuse 25 A
further information internet links	
internet link	
<ul style="list-style-type: none"> to website: Industry Mall to web page: selection aid TIA Selection Tool to web page: power supplies to website: CAX-Download-Manager to website: Industry Online Support 	https://mall.industry.siemens.com https://www.siemens.com/tstcloud https://siemens.com/sitop https://www.siemens.com/cax https://support.industry.siemens.com
additional information	


other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)
-------------------	---

security information	
security information	<p>Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement – and continuously maintain – a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry. Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under https://www.siemens.com/cert. (V4.7)</p>

Classifications			
		Version	Classification
	eClass	14	27-05-04-03
	eClass	12	27-05-04-03
	eClass	9.1	27-05-04-03
	eClass	9	27-05-04-03
	eClass	8	27-05-04-03
	eClass	7.1	27-05-04-03
	eClass	6	27-05-04-90
	ETIM	10	EC000357
	ETIM	9	EC000357
	ETIM	8	EC000357
	ETIM	7	EC000357
	UNSPSC	15	26-11-17-01

Approvals Certificates	
General Product Approval	Maritime application

Manufacturer Declaration	Declaration of Conformity				
		EG-Konf.	UL	RCM	ABS

Maritime application	Dangerous goods	Environment
	Dangerous goods information	

last modified:	11/25/2025 
----------------	--