

**VALVE PLUG SUPPRESSOR FORM C - 8MM**

Zener diode and LED, 24VAC/DC/100VA/W

Art.No.: 3124833

Weight: 0.008



Country of origin: CZ

Model designation: MVK-ZLU 24

24 V AC/DC

Z-Diode + LED

Remove plug gasket when fitting adapter. Other LED colors on request.

**[Link to Product](#)****Illustration**

Product may differ from Image

**Commercial data**

|             |                                                                                               |
|-------------|-----------------------------------------------------------------------------------------------|
| URL Webshop | <a href="https://shop.murrelektronik.com/3124833">https://shop.murrelektronik.com/3124833</a> |
| GTIN        | 4048879011570                                                                                 |
| ECLASS-6.0  | 27371013                                                                                      |
| ECLASS-6.1  | 27371013                                                                                      |

|               |               |
|---------------|---------------|
| ECLASS-7.0    | 27371013      |
| ECLASS-7.1    | 27371013      |
| ECLASS-8.0    | 27371013      |
| ECLASS-8.1    | 27371013      |
| ECLASS-9.0    | 27371013      |
| ECLASS-9.1    | 27371013      |
| ECLASS-10.0.1 | 27371013      |
| ECLASS-10.1   | 27371013      |
| ECLASS-11.0   | 27371013      |
| ECLASS-11.1   | 27371013      |
| ECLASS-12.0   | 27371013      |
| ECLASS-13.0   | 27371013      |
| ECLASS-14.0   | 27371013      |
| ETIM-5.0      | EC000683      |
| ETIM-6.0      | EC000683      |
| ETIM-7.0      | EC000683      |
| ETIM-8.0      | EC000683      |
| EAN           | 4048879011570 |

**Electrical data**

|                          |       |
|--------------------------|-------|
| Drop-out delay time max. | 20 ms |
| Holding power max.       | 100 W |

**Electrical data | Supply**

|                           |      |
|---------------------------|------|
| Cut-off peak voltage max. | 55 V |
|---------------------------|------|

**Electrical data | Input**

|                       |      |
|-----------------------|------|
| Input voltage AC min. | 18 V |
| Input voltage AC max. | 30 V |
| Input voltage DC min. | 18 V |
| Input voltage DC max. | 30 V |

**Diagnostics**

|                       |        |
|-----------------------|--------|
| Status indication LED | yellow |
|-----------------------|--------|

**Device protection | Media**

|                  |                 |
|------------------|-----------------|
| Flame resistance | flame retardant |
|------------------|-----------------|

**Mechanical data | Material data**

|                  |               |
|------------------|---------------|
| Material housing | PA            |
| Color housing    | black         |
| Material contact | Bronze        |
| Coating contact  | silver-plated |

**Mechanical data | Mounting data**

|        |         |
|--------|---------|
| Height | 27 mm   |
| Width  | 27.5 mm |
| Depth  | 15.5 mm |

**Environmental characteristics | Climatic**

|                                          |        |
|------------------------------------------|--------|
| Operating temperature min.               | -20 °C |
| Operating temperature max.               | 60 °C  |
| Housing temperature max. (EN 61347-2-13) | 130 °C |