

**Modlink MSDD-set: Frame 4000-68123-0000000,**


insert 4000-68000-1440000

Art.No.: 4000-68123-1440000

Weight: 0.632

Country of origin: CZ

Model designation: MSDD\_2MV\_9B/B+RJ45+USB\_

**[Link to Product](#)****Illustration**

Product may differ from Image

0  
0  
0  
0  
0  
0  
0  
0  
0



0

0

0

| Header                                        |                                                                                                                     |
|-----------------------------------------------|---------------------------------------------------------------------------------------------------------------------|
| Material short text                           | MSDD_2MV_9B/B+RJ45+USB_                                                                                             |
| Commercial data                               |                                                                                                                     |
| URL Webshop                                   | <a href="https://shop.murrelektronik.com/4000-68123-1440000">https://shop.murrelektronik.com/4000-68123-1440000</a> |
| GTIN                                          | 4048879033763                                                                                                       |
| ECLASS-6.0                                    | 27189217                                                                                                            |
| ECLASS-6.1                                    | 27189217                                                                                                            |
| ECLASS-7.0                                    | 27189217                                                                                                            |
| ECLASS-7.1                                    | 27189217                                                                                                            |
| ECLASS-8.0                                    | 27189217                                                                                                            |
| ECLASS-8.1                                    | 27189217                                                                                                            |
| ECLASS-9.0                                    | 27182806                                                                                                            |
| ECLASS-9.1                                    | 27189217                                                                                                            |
| ECLASS-10.0.1                                 | 27182806                                                                                                            |
| ECLASS-10.1                                   | 27182806                                                                                                            |
| ECLASS-11.0                                   | 27182806                                                                                                            |
| ECLASS-11.1                                   | 27182806                                                                                                            |
| ECLASS-12.0                                   | 27182806                                                                                                            |
| ECLASS-13.0                                   | 27182806                                                                                                            |
| ECLASS-14.0                                   | 27182806                                                                                                            |
| ETIM-5.0                                      | EC002625                                                                                                            |
| ETIM-6.0                                      | EC002625                                                                                                            |
| ETIM-7.0                                      | EC002625                                                                                                            |
| ETIM-8.0                                      | EC002625                                                                                                            |
| customs tariff number                         | 85366990                                                                                                            |
| EAN                                           | 4048879033763                                                                                                       |
| Packaging unit                                | 1                                                                                                                   |
| Frame                                         |                                                                                                                     |
| Material housing                              | Fine zinc die casting                                                                                               |
| Coating housing                               | surface finished                                                                                                    |
| Suitable for installation wall thickness min. | 1 mm                                                                                                                |
| Suitable for installation wall thickness max. | 5 mm                                                                                                                |
| Degree of protection (EN IEC 60529)           | IP65                                                                                                                |
| Operating temperature min.                    | -10 °C                                                                                                              |
| Operating temperature max.                    | 60 °C                                                                                                               |
| Storage temperature min.                      | -25 °C                                                                                                              |
| Shielding plate                               |                                                                                                                     |
| Connection information                        | Threaded hole M4                                                                                                    |
| Tightening torque                             | 0.9 Nm                                                                                                              |
| Tightening torque tolerance                   | ± 0.1 Nm                                                                                                            |
| USB                                           |                                                                                                                     |
| USB specification                             | 3.0                                                                                                                 |
| Looking techniques                            | Snap-in connector                                                                                                   |
| Data transmission rate max.                   | 5,000 Mbit/s                                                                                                        |
| Operating voltage AC                          | 48 V                                                                                                                |
| Operating voltage DC                          | 48 V                                                                                                                |

|                                       |        |
|---------------------------------------|--------|
| Operating current                     | 1.5 A  |
| Operating voltage AC max. (UL-listed) | 30 V   |
| Operating voltage DC max. (UL-listed) | 42.4 V |

**SUB-D9**

|                                       |                                                |
|---------------------------------------|------------------------------------------------|
| Family construction form              | SUB-D9                                         |
| Gender                                | female                                         |
| No. of poles                          | 9                                              |
| Looking techniques                    | Standard UNC 4-40 screw thread bolt (EN 60807) |
| Family type Back side                 | SUB-D9                                         |
| Gender Rear                           | female                                         |
| Operating voltage AC                  | 48 V                                           |
| Operating voltage DC                  | 48 V                                           |
| Operating current                     | 3 A                                            |
| Operating voltage AC max. (UL-listed) | 30 V                                           |
| Operating voltage DC max. (UL-listed) | 42.4 V                                         |
| Current operating max. (UL)           | 175 mA                                         |

**RJ45**

|                                       |                   |
|---------------------------------------|-------------------|
| Family construction form              | RJ45              |
| Looking techniques                    | Snap-in connector |
| Cable category min.                   | Cat5e             |
| Family type Back side                 | RJ45              |
| Operating voltage AC max. (UL-listed) | 30 V              |
| Operating voltage DC max. (UL-listed) | 42.4 V            |
| Current operating max. (UL)           | 175 mA            |