

Modlink MSDD-set: Frame 4000-68213-0000000,


insert 4000-68000-1430000

Art.No.: 4000-68213-1430000

Weight: 0.233

Country of origin: CZ

Model designation: MSDD_1MVIPK_9B/S+RJ45+USB_

Link to Product**Illustration**

Product may differ from Image

0
0
0
0
0
0
0
0
0

0

0

0

Header	
Material short text	MSDD_1MVIK_9B/S+RJ45+USB_
Commercial data	
URL Webshop	https://shop.murrelektronik.com/4000-68213-1430000
GTIN	4048879033404
ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-7.1	27189217
ECLASS-8.0	27189217
ECLASS-8.1	27189217
ECLASS-9.0	27182806
ECLASS-9.1	27189217
ECLASS-10.0.1	27182806
ECLASS-10.1	27182806
ECLASS-11.0	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ECLASS-13.0	27182806
ECLASS-14.0	27182806
ETIM-5.0	EC002625
ETIM-6.0	EC002625
ETIM-7.0	EC002625
ETIM-8.0	EC002625
customs tariff number	85366990
EAN	4048879033404
Packaging unit	1
Frame	
Material housing	Fine zinc die casting
Material lid	PC
Coating housing	surface finished
Color cover	transparent
Suitable for installation wall thickness min.	1 mm
Suitable for installation wall thickness max.	5 mm
Degree of protection (EN IEC 60529)	IP65
Operating temperature min.	-10 °C
Operating temperature max.	60 °C
Storage temperature min.	-25 °C
Shielding plate	
Connection information	Threaded hole M4
Tightening torque	0.9 Nm
Tightening torque tolerance	± 0.1 Nm
USB	
USB specification	3.0
Looking techniques	Snap-in connector

Data transmission rate max.	5,000 Mbit/s
Operating voltage AC	48 V
Operating voltage DC	48 V
Operating current	1.5 A
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42.4 V

SUB-D9

Family construction form	SUB-D9
Gender	female
No. of poles	9
Looking techniques	Standard UNC 4-40 screw thread bolt (EN 60807)
Family type Back side	SUB-D9
Gender Rear	male
Operating voltage AC	48 V
Operating voltage DC	48 V
Operating current	3 A
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42.4 V
Current operating max. (UL)	175 mA

RJ45

Family construction form	RJ45
Looking techniques	Snap-in connector
Cable category min.	Cat5e
Family type Back side	RJ45
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42.4 V
Current operating max. (UL)	175 mA