

EOL - Modlink MSDD-set: Frame 4000-68522-0000001,

discontinued - End of Life Date: 2024-12-31


Art.No.: 4000-68522-4313001
Weight: 0.303
Country of origin: DE
Model designation: X MSDD_2transparent_France+RJ45+USB+FI-A

Link to Product

Illustration



Product may differ from Image



Commercial data

ECLASS-6.0	27189217
ECLASS-7.0	27189217
ECLASS-8.0	27189217
ECLASS-9.0	27189217
ETIM-5.0	EC002625
customs tariff number	85366990

customs tariff number	85366990
customs tariff number	85366990
customs tariff number	85366990
EAN	4048879445900
EAN	4048879445900
EAN	4048879445900
EAN	4048879445900
Packaging unit	1
Packaging unit	1
Packaging unit	1
Packaging unit	1

Frame

Degree of protection (EN IEC 60529)	IP65
Operating temperature min.	-30 °C
Operating temperature max.	70 °C
Storage temperature min.	-30 °C
Storage temperature max.	80 °C
Suitable for installation wall thickness min.	1 mm
Suitable for installation wall thickness max.	5 mm
Material housing	PA
Color housing	black
Material lid	PC
Color cover	transparent

Shielding plate

Connection information	Threaded hole M4
Tightening torque	0,9 Nm

France (UTE-NF)

Connection cross section max.	4 mm²
AWG number max.	12
Operating voltage AC	250 V
Operating current	16 A
Connection	Screw terminals SK
No. of poles	2 + PE
Connections per pole	2
Protection contact present	yes

USB

Operating voltage AC	48 V
Operating voltage DC	48 V
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Operating current	1,5 A
USB specification	3.0
Data transmission rate max.	5000 MBit/s
Looking techniques	Snap-in connector

RJ45

Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Current operating max. (UL)	175 mA
Family construction form	RJ45
Family type Back side	RJ45
Cable category min.	Cat5e

Looking techniques

Snap-in connector