

Modlink MSDD-set: Frame 4000-68523-0000001,

insert 4000-68000-4120000

Art.No.: 4000-68523-4120001

Weight: 0.541

Country of origin: US

Model designation: MSDD_2metallic_GFCI 15A+2xRJ45+3A fuse_

with touch protection

[Link to Product](#)**Illustration**

Product may differ from Image

0
0
0
0
0
0
0

0

0

0

0

Header	
Material short text	MSDD_2metallic_GFCI 15A+2xRJ45+3A fuse_
Commercial data	
URL Webshop	https://shop.murrelektronik.com/4000-68523-4120001
GTIN	4048879477970
ECLASS-6.0	27144001
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-7.1	27189217
ECLASS-8.0	27189217
ECLASS-8.1	27189217
ECLASS-9.0	27182806
ECLASS-9.1	27189217
ECLASS-10.0.1	27182806
ECLASS-10.1	27182806
ECLASS-11.0	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ECLASS-13.0	27182806
ECLASS-14.0	27182806
ETIM-5.0	EC002625
ETIM-6.0	EC002625
ETIM-7.0	EC002625
ETIM-8.0	EC002625
customs tariff number	85366990
EAN	4048879477970
Packaging unit	1
Mechanical data Mounting data	
Height	88 mm
Width	116 mm
Depth	72 mm
Frame	
Material housing	PA
Color housing	Black
Material lid	ABS
Color cover	metallic
Suitable for installation wall thickness min.	1 mm
Suitable for installation wall thickness max.	5 mm
Degree of protection (EN IEC 60529)	IP65
Operating temperature min.	-30 °C
Operating temperature max.	70 °C
Storage temperature min.	-30 °C
Fuse	
Operating voltage AC	250 V

Operating voltage DC	32 V
----------------------	------

Nominal current	3 A
-----------------	-----

USA

Connection	Screw terminals SK
------------	--------------------

No. of poles	PE
--------------	----

Connections per pole	2
----------------------	---

Protection contact present	yes
----------------------------	-----

Connection cross section max.	6 mm ²
-------------------------------	-------------------

AWG number max.	10
-----------------	----

Operating voltage AC	125 V
----------------------	-------

Operating current	15 A
-------------------	------

RJ45

Family construction form	RJ45
--------------------------	------

Looking techniques	Snap-in connector
--------------------	-------------------

Cable category min.	Cat5e
---------------------	-------

Family type Back side	RJ45
-----------------------	------

Operating voltage AC max. (UL-listed)	30 V
---------------------------------------	------

Operating voltage DC max. (UL-listed)	42.4 V
---------------------------------------	--------

Current operating max. (UL)	175 mA
-----------------------------	--------