

IO-Link / analog converter

AI Multi PT / RTD, M12, straight

Art.No.: 5000-00501-1500001

Weight: 0.045


Country of origin: DE

Model designation: IOL AI-RTD-V2-MULT-PAR


IO-Link / analog converter

AI Multi PT/RTD, M12


16Bit, IP65/67, IO-Link V1.1, Class A


[Link to Product](#)**Illustration****Male**

PIN 1: +24 V (L+)
 PIN 2: n.c.
 PIN 3: GND
 PIN 4: C/Q, IO-Link

Female

PIN 1: RD 1
 PIN 2: RD 2
 PIN 3: WH 1
 PIN 4: WH 2
 PIN 5: n.c.





Product may differ from Image



Header	
Material short text	IOL AI-RTD-V2-MULT-PAR
Commercial data	
URL Webshop	https://shop.murrelektronik.com/5000-00501-1500001
GTIN	4048879588478
ECLASS-6.0	27242601
ECLASS-6.1	27242602
ECLASS-7.0	27242602
ECLASS-7.1	27242602
ECLASS-8.0	27242602
ECLASS-8.1	27242602
ECLASS-9.0	27242602
ECLASS-9.1	27242602
ECLASS-10.0.1	27242602
ECLASS-10.1	27242602
ECLASS-11.0	27242602
ECLASS-11.1	27242602
ECLASS-12.0	27242602
ECLASS-13.0	27242602
ECLASS-14.0	27242602
ETIM-5.0	EC001596
ETIM-6.0	EC001596
ETIM-7.0	EC001596
ETIM-8.0	EC001596
customs tariff number	85437090
EAN	4048879588478
Packaging unit	1
Electrical data Supply	
Norm operating voltage	EN 61131-2
Operating voltage DC	24 V
Operating voltage DC min.	18 V
Operating voltage DC max.	30 V
Operating voltage US DC	24 V

Current consumption max. 15 mA

Electrical data | Input

Current carrying capacity max. 0.2 A

Parameterizable input averaging filter process data yes

Conversion time with net suppression OFF: 10 ms, 50 Hz: 60 ms, 60 Hz: 100 ms

Industrial communication | IO-Link

Port Class A

IO-Link revision ID V1.1

IO-Link transmission rate COM2 (38.4 kbit/s)

IO-Link process data length input 2 bytes

IO-Link cycle time min. 10 ms

Diagnostics

Short circuit diagnosis yes

Overload diagnosis yes

Temperature control yes

Diagnostic via IO-Link yes

Diagnostic via LED yes

LED display Ethernet connection/data traffic

IO-Link events Undervoltage supply, lower limit, upper limit, Overvoltage supply, Override, Overcurrent sensor supply, Overtemperature, Device defect

Device protection | Electrical

Degree of protection (EN IEC 60529) IP67, IP65

Invers-polarity protection yes

Over voltage protection yes

Short circuit protection sensor supply yes

Resistance to loads with regenerative power yes

Mechanical data | Material data

Material housing Plastic

Mechanical data | Mounting data

Height 32.3 mm

Width 77.2 mm

Depth 15 mm

Environmental characteristics | Climatic

Operating temperature min. -30 °C

Operating temperature max. 70 °C

Storage temperature min. -40 °C

Storage temperature max. 85 °C

Connection type 2

Connection type 1 AI

Connection type 2 IO-Link Port

Family construction form M12

No. of poles 5

Coding A

Gender female

Color contact carrier black

PIN 1 RD 1

PIN 2 RD 2

PIN 3 WH 1

PIN 4 WH 2

PIN 5 n.c.

Family construction form	M12
No. of poles	4
Coding	A
Gender	male
Color contact carrier	black
PIN 1	24 V DC (L +)
PIN 2	n.c.
PIN 3	0 V (L -)
PIN 4	C / Q / IO-Link