

Connection 2x profile- to 2x profile cable

Weight: 0.659

Country of origin: DE

Model designation: MASI67 Verkn. 2x auf 2x Profilkabel

Link to Product

A black, square-shaped electronic component, likely a sensor or actuator, with four yellow wires extending from it. The component has four screws on its top surface and a green label with text.

Technical drawing of a mechanical part (Fig. 1.10) showing a 3D perspective view. The part is a rectangular block with a central circular feature and four small circular features. The dimensions are: 60 (width), 90 (length), and 26 (height).



Material short text	MAI67 Verkn. 2x auf 2x Profilkabel
---------------------	------------------------------------

URL Webshop	https://shop.murrelektronik.com/55033
GTIN	4048879052184
ECLASS-6.0	27400209
ECLASS-6.1	27279219
ECLASS-7.0	27279219
ECLASS-7.1	27279219
ECLASS-8.0	27279219
ECLASS-8.1	27279219
ECLASS-9.0	27440111
ECLASS-10.0.1	27440111
ECLASS-10.1	27440111
ECLASS-11.0	27440111
ECLASS-11.1	27440111
ECLASS-12.0	27440111
ECLASS-13.0	27440111
ECLASS-14.0	27440111
ETIM-5.0	EC001583

Murrelektronik GmbH | Grabenstraße 29 | 71570 Oppenweiler | Fon +49 (71 91) 47-0 | Fax +49 (71 91) 47-491000 | shop@murrelektronik.com | shop.murrelektronik.com

ETIM-6.0	EC001583
ETIM-7.0	EC001583
ETIM-8.0	EC001583
customs tariff number	85369010
EAN	4048879052184
Packaging unit	1

Electrical data | Supply

Operating voltage DC max.	36 V
Total current max.	8 A

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP67
Insulation strength ASI/Power	200 V

Mechanical data | Mounting data

Height	90 mm
Width	74 mm
Depth	26 mm
Mounting method	geschnappt, screwed
Suitable for mounting type	(EN 60715), mounting rail

Environmental characteristics | Climatic

Operating temperature min.	-20 °C
Operating temperature max.	60 °C
Storage temperature min.	-40 °C
Storage temperature max.	80 °C