



SIMATIC ET 200SP, Analog input module, AI 2x U/I 2-/4-wire High Feat., suitable for BU type A0, A1, Color code CC05, channel diagnostics, 16 bit, +/-0.1%

General information	
Product type designation	AI 2xU/I 2-/4-wire HF
HW functional status	From FS06
Firmware version	
• FW update possible	Yes
usable BaseUnits	BU type A0, A1
Color code for module-specific color identification plate	CC03
Product function	
• I&M data	Yes; I&M0 to I&M3
• Isochronous mode	Yes; 250 µs
• Measuring range scalable	No
Engineering with	
• STEP 7 TIA Portal configurable/integrated from version	V13
• STEP 7 configurable/integrated from version	V5.5 / -
• PCS 7 configurable/integrated from version	V8.1 SP1
• PROFIBUS from GSD version/GSD revision	One GSD file each, Revision 3 and 5 and higher
• PROFINET from GSD version/GSD revision	GSDML V2.3
Operating mode	
• Oversampling	No
• MSI	Yes
CiR - Configuration in RUN	
Reparameterization possible in RUN	Yes
Calibration possible in RUN	Yes
Supply voltage	
Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes
Input current	
Current consumption (rated value)	39 mA; without sensor supply
Encoder supply	
24 V encoder supply	
• 24 V	Yes
• Short-circuit protection	Yes
• Output current, max.	20 mA; max. 50 mA per channel for a duration < 10 s (two-wire)
Additional 24 V encoder supply	
• Short-circuit protection	Yes; channel by channel
• Output current, max.	100 mA; max. 150 mA for a duration of < 10 s (four-wire)
Power loss	
Power loss, typ.	0.95 W; without sensor supply

Address area	
Address space per module	
• Address space per module, max.	4 byte; + 4 byte for scaling of measured values, + 1 byte for QI information
Hardware configuration	
Automatic encoding	Yes
• Mechanical coding element	Yes
• Type of mechanical coding element	Type A
Selection of BaseUnit for connection variants	
• 2-wire connection	BU type A0, A1
• 4-wire connection	BU type A0, A1
Analog inputs	
Number of analog inputs	2; Differential inputs
• For current measurement	2
• For voltage measurement	2
permissible input voltage for voltage input (destruction limit), max.	30 V
permissible input current for current input (destruction limit), max.	50 mA
Analog input with oversampling	No
Standardization of measured values	Yes
Input ranges (rated values), voltages	
• 0 to +10 V	Yes; 15 bit
— Input resistance (0 to 10 V)	75 kΩ
• 1 V to 5 V	Yes; 15 bit
— Input resistance (1 V to 5 V)	75 kΩ
• -10 V to +10 V	Yes; 16 bit incl. sign
— Input resistance (-10 V to +10 V)	75 kΩ
• -5 V to +5 V	Yes; 16 bit incl. sign
— Input resistance (-5 V to +5 V)	75 kΩ
Input ranges (rated values), currents	
• 0 to 20 mA	Yes; 15 bit
— Input resistance (0 to 20 mA)	130 Ω
• -20 mA to +20 mA	Yes; 16 bit incl. sign
— Input resistance (-20 mA to +20 mA)	130 Ω
• 4 mA to 20 mA	Yes; 15 bit
— Input resistance (4 mA to 20 mA)	130 Ω
Cable length	
• shielded, max.	1 000 m; 200 m for voltage measurement
Analog value generation for the inputs	
Measurement principle	Sigma Delta
Integration and conversion time/resolution per channel	
• Resolution with overrange (bit including sign), max.	16 bit
• Integration time, parameterizable	Yes
• Integration time (ms)	67.5 / 22.5 / 18.75 / 10 / 5 / 2.5 / 1.25 / 0.625 ms
• Basic conversion time, including integration time (ms)	68.03 / 22.83 / 19.03 / 10.28 / 5.23 / 2.68 / 1.43 / 0.730 ms
• Interference voltage suppression for interference frequency f1 in Hz	16.6 / 50 / 60 / 300 / 600 / 1 200 / 2 400 / 4 800
• Conversion time (per channel)	68.2 / 23 / 19.2 / 10.45 / 5.40 / 2.85 / 1.6 / 0.9 ms
• Basic execution time of the module (all channels released)	1 ms
Smoothing of measured values	
• Number of smoothing levels	6; none; 2-/4-/8-/16-/32-fold
• parameterizable	Yes
Encoder	
Connection of signal encoders	
• for voltage measurement	Yes
• for current measurement as 2-wire transducer	Yes
— Burden of 2-wire transmitter, max.	650 Ω
• for current measurement as 4-wire transducer	Yes
Errors/accuracies	
Linearity error (relative to input range), (+/-)	0.01 %
Temperature error (relative to input range), (+/-)	0.003 %/K

Crosstalk between the inputs, min.	-50 dB		
Repeat accuracy in steady state at 25 °C (relative to input range), (+/-)	0.01 %		
Operational error limit in overall temperature range			
• Voltage, relative to input range, (+/-)	0.1 %		
• Current, relative to input range, (+/-)	0.1 %		
Basic error limit (operational limit at 25 °C)			
• Voltage, relative to input range, (+/-)	0.05 %; 0.1 % at SFU 4.8 kHz		
• Current, relative to input range, (+/-)	0.05 %; 0.1 % at SFU 4.8 kHz		
Interference voltage suppression for $f = n \times (f_1 \pm 1 \%)$, f_1 = interference frequency			
• Common mode voltage, max.	35 V		
• Common mode interference, min.	90 dB		
Isochronous mode			
Filtering and processing time (TCI), min.	800 μs		
Bus cycle time (TDP), min.	1 ms		
Jitter, max.	5 μs		
Interrupts/diagnostics/status information			
Diagnostics function	Yes		
Alarms			
• Diagnostic alarm	Yes		
• Limit value alarm	Yes; two upper and two lower limit values in each case		
Diagnoses			
• Monitoring the supply voltage	Yes		
• Wire-break	Yes; Measuring range 4 to 20 mA only		
• Short-circuit	Yes; channel-by-channel, at 1 to 5 V or for short-circuit in encoder supply		
• Group error	Yes		
• Overflow/underflow	Yes		
Diagnostics indication LED			
• Monitoring of the supply voltage (PWR-LED)	Yes; green PWR LED		
• Channel status display	Yes; green LED		
• for channel diagnostics	Yes; red LED		
• for module diagnostics	Yes; green/red DIAG LED		
Potential separation			
Potential separation channels			
• between the channels	Yes		
• between the channels and backplane bus	Yes		
• between the channels and the power supply of the electronics	Yes		
Isolation			
Isolation tested with	707 V DC (type test)		
Ambient conditions			
Ambient temperature during operation			
• horizontal installation, min.	-30 °C; < 0 °C as of FS06		
• horizontal installation, max.	60 °C		
• vertical installation, min.	-30 °C; < 0 °C as of FS06		
• vertical installation, max.	50 °C		
Altitude during operation relating to sea level			
• Installation altitude above sea level, max.	5 000 m; Restrictions for installation altitudes > 2 000 m, see manual		
Dimensions			
Width	15 mm		
Height	73 mm		
Depth	58 mm		
Weights			
Weight, approx.	32 g		
Classifications			
		Version	Classification
	eClass	14	27-24-26-01
	eClass	12	27-24-26-01
	eClass	9.1	27-24-26-01
	eClass	9	27-24-26-01

eClass	8	27-24-26-01
eClass	7.1	27-24-26-01
eClass	6	27-24-26-01
ETIM	10	EC001596
ETIM	9	EC001596
ETIM	8	EC001596
ETIM	7	EC001596
IDEA	4	3562
UNSPSC	15	32-15-17-05

Approvals / Certificates

General Product Approval

[Manufacturer Declaration](#)





[Miscellaneous](#)



[KC](#)

General Product Approval For use in hazardous locations

[Metrological Approval](#)





[CCC-Ex](#)

[FM](#)



For use in hazardous locations Maritime application



[Miscellaneous](#)









Maritime application Environment

[NK / Nippon Kaiji Kyokai](#)





[CCS \(China Classification Society\)](#)





last modified:

4/10/2025