



plug-in relay complete unit, 4 changeover contacts, 230 V AC, LED module red, base with logical isolation, spring-loaded terminal (push-in)

product brand name	SIRIUS
product designation	Coupling relay with plug-in relay
product type designation	LZS
General technical data	
display version LED	Yes
percental drop-out voltage related to the input voltage	30 %
operating frequency without load	36 000 1/h
operating frequency with load	360 1/h
switching behavior	monostable
mechanical service life (operating cycles) typical	20 000 000
electrical endurance (operating cycles) at AC-15 at 230 V typical	250 000
thermal current	6 A
reference code according to IEC 81346-2	K
Substance Prohibitance (Date)	05/01/2012
Weight	0.108 kg
Control circuit/ Control	
control supply voltage at AC	
• at 50 Hz rated value	230 V
• at 60 Hz rated value	230 V
control supply voltage frequency	
• 1 rated value	50 Hz
• 2 rated value	60 Hz
supply voltage frequency for auxiliary and control circuit rated value	50 ... 60 Hz
operating range factor control supply voltage rated value at AC at 50 Hz	
• initial value	0.9
• full-scale value	1.1
operating range factor control supply voltage rated value at AC at 60 Hz	
• initial value	0.9
• full-scale value	1.1
Switching Function	
design of the switching function	changeover switch
Mechanical data	
product component plug-in socket	Yes
design of the snap-on socket base	Socket with logic isolation
design of the relay operating mechanism	poled
Short-circuit protection	
design of the fuse link for short-circuit protection of the auxiliary	fuse gG: 6 A

switch required			
Auxiliary circuit			
type of switching contact	Changeover contact		
material of switching contacts	AgNi 90/10		
number of NC contacts for auxiliary contacts	0		
number of NO contacts for auxiliary contacts	0		
number of CO contacts for auxiliary contacts	4		
operational current of auxiliary contacts at AC-15			
• at 250 V	2 A		
operational current at DC-13 at 24 V rated value	4 A		
operational current of auxiliary contacts at DC-13			
• at 24 V	4 A		
Main circuit			
type of voltage	AC		
ampacity of the output relay at DC-13			
• at 24 V	4 A		
Display			
display version as status display by LED	LED red		
Connections/ Terminals			
product function removable terminal	No		
type of electrical connection	spring-loaded terminals		
type of connectable conductor cross-sections			
• solid	1x (0,75 ... 1,5), 2x (0,75 ... 1,0), 2x 1,5		
• finely stranded with core end processing	1x (0,75 ... 1,5), 2x 0,75		
• finely stranded without core end processing	1x (0,75 ... 1,5), 2x (0,75 ... 1,0), 2x 1,5		
• for AWG cables solid	1x (18 ... 16), 2x (18 ... 16)		
• for AWG cables stranded	1x (18 ... 16), 2x (18 ... 16)		
connectable conductor cross-section			
• solid	0.75 ... 1.5 mm ²		
• finely stranded with core end processing	0.75 ... 1.5 mm ²		
• finely stranded without core end processing	0.75 ... 1.5 mm ²		
AWG number as coded connectable conductor cross section			
• solid	18 ... 16		
• stranded	18 ... 16		
Installation/ mounting/ dimensions			
mounting position	any		
fastening method	snap-on mounting		
height	98 mm		
width	28 mm		
depth	79 mm		
Ambient conditions			
ambient temperature			
• during operation	-40 ... +70 °C		
• during storage	-25 ... +70 °C		
• during transport	-25 ... +70 °C		
Approvals Certificates			
<table> <tr> <td>General Product Approval</td><td>other</td></tr> </table>		General Product Approval	other
General Product Approval	other		



[Confirmation](#)

Environment

[Environmental Con-
firmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=LZS:PT5D5T30>

Cax online generator


<http://support.automation.siemens.com/VW/CAXorder/default.aspx?lang=en&mlfb=LZS:PT5D5T30>


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/LZS:PT5D5T30>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=LZS:PT5D5T30&lang=en





last modified:

4/2/2025 