

8 Port unmanaged Gigabit Switch 4 PoE Ports IP20 metal

Art.No.: 58192
Weight: 0.7
Country of origin: TW
Model designation: TREE 8TX 4PoE GE


8 Port Unmanaged IP20 PoE Gigabit Switch
24 V power supply
4 PoE ports

Link to Product

Illustration



Product may differ from Image



Header

Material short text TREE 8TX 4PoE GE

Commercial data

URL Webshop	https://shop.murrelektronik.com/58192
GTIN	4048879845090
ECLASS-6.1	19170106
ECLASS-7.0	19170106
ECLASS-7.1	19170106
ECLASS-8.0	19170106
ECLASS-8.1	19170106
ECLASS-9.0	19170402
ECLASS-9.1	19170106
ECLASS-10.0.1	19170402
ECLASS-10.1	19170402
ECLASS-11.0	19170402
ECLASS-11.1	19170402
ECLASS-12.0	19170402
ECLASS-13.0	19170402
ECLASS-14.0	19170402
customs tariff number	85176200

EAN	4048879845090
-----	---------------

Packaging unit	1
----------------	---

Electrical data | Supply

Operating voltage DC min.	12 V
---------------------------	------

Operating voltage DC max.	57 V
---------------------------	------

PoE voltage amplifier	yes
-----------------------	-----

Industrial communication

Data transmission rate max.	1,000 Mbit/s
-----------------------------	--------------

Industrial communication | Ethernet functionality

VLAN unmanaged (IEEE 802.1Q)	no
------------------------------	----

Switch type	unmanaged
-------------	-----------

duplex	Full duplex
--------	-------------

Auto-negotiation	yes
------------------	-----

Auto-crossover	yes
----------------	-----

Diagnostics

Alarm contact	yes
---------------	-----

Diagnostic	No voltage
------------	------------

LED display	Ethernet connection/data traffic
-------------	----------------------------------

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP20
-------------------------------------	------

Mechanical data | Material data

Material housing	Metal
------------------	-------

Color housing	black
---------------	-------

Mechanical data | Mounting data

Height	145 mm
--------	--------

Width	57.8 mm
-------	---------

Depth	113 mm
-------	--------

Mounting method	geschnappt
-----------------	------------

Suitable for mounting type	Mounting rail TH35, (EN 60715)
----------------------------	--------------------------------

Environmental characteristics | Climatic

Operating temperature min.	-40 °C
----------------------------	--------

Operating temperature max.	70 °C
----------------------------	-------

Storage temperature min.	-40 °C
--------------------------	--------

Storage temperature max.	85 °C
--------------------------	-------

Connection type 2

Connection type 1	8
-------------------	---

Connection type 2	X1
-------------------	----

Family construction form	RJ45
--------------------------	------

No. of poles	8
--------------	---

Gender	female
--------	--------

Color contact carrier	black
-----------------------	-------

PIN 1	TD +
-------	------

PIN 2	TD -
-------	------

PIN 3	RD +
-------	------

PIN 4	n.c.
-------	------

PIN 5	n.c.
-------	------

PIN 6	RD -
-------	------

PIN 7	n.c.
-------	------

PIN 8	n.c.
-------	------

Family construction form	terminal
--------------------------	----------

No. of poles	7
--------------	---

Gender	male
Color contact carrier	green
Connection	Plug-in terminals RK
PIN 1	FE
PIN 2	V 1 -
PIN 3	V 1 +
PIN 4	Relay (NO)
PIN 5	Relay (NO)
PIN 6	V 2 -
PIN 7	V 2 +