

MVP12-P6 DIO8 DIO8 8xM12A IOLB12 B0

IO-Link Class B I/O module

Art.No.: 59718

Weight: 0.2

Country of origin: DE

Model designation: MVP12-P6 DIO8 DIO8 8xM12A IOLB12 B0

IO-Link hub in 50 mm plastic housing

1 × M12 IO-Link Class B



8 × M12 I/O

16 configurable digital inputs/outputs

Galvanically isolated voltage groups

Preconfigured parameter range

Connection cables are in the online shop under "Connection Technology".

[Link to Product](#)**Illustration**

Product may differ from Image

**Header**

Material short text MVP12-P6 DIO8 DIO8 8xM12A IOLB12 B0

Commercial data	
URL Webshop	https://shop.murrelektronik.com/59718
GTIN	4048879865043
ECLASS-6.0	27242604
ECLASS-6.1	27242604
ECLASS-7.0	27242604
ECLASS-7.1	27242604
ECLASS-8.0	27242604
ECLASS-8.1	27242604
ECLASS-9.0	27242604
ECLASS-9.1	27242604
ECLASS-10.0.1	27242604
ECLASS-10.1	27242604
ECLASS-11.0	27242604
ECLASS-11.1	27242604
ECLASS-12.0	27242604
ECLASS-13.0	27242604
ECLASS-14.0	27242604
customs tariff number	85389099
EAN	4048879865043
Packaging unit	1
Electrical data Supply	
Operating voltage DC	24 V
Operating voltage US DC	24 V
Operating voltage US DC min.	18 V
Operating voltage US DC max.	30 V
Total current US max.	4 A
Operating voltage UA DC	24 V
Operating voltage UA DC min.	18 V
Operating voltage UA DC max.	30 V
Total current UA max.	4 A
Current consumption max.	50 mA
Electrical data Input	
Sensor current per input max.	0.5 A
Input filter time	1 ms
Type input	Type 3, Type 1
Electrical data Output	
Output current per pin max.	2 A
Industrial communication IO-Link	
IO-Link type	Device
Port Class	B
IO-Link revision ID	V1.1.2
IO-Link transmission rate	COM3 (230.4 kbit/s)
IO-Link process data length input	2 bytes
IO-Link process data length output	2 bytes
IO-Link cycle time min.	1 ms
IO-Link revision compatibility	V1.1.3
Diagnostics	
Actuator warning	yes
Short circuit diagnosis	yes

Overload diagnosis	yes
Diagnostic via LED	per module and channel
Status indication LED	green
LED display	Ethernet connection/data traffic
IO-Link events	Undervoltage supply, No voltage

Device protection | Electrical

Installation height max. ASL	3,000 m
Degree of protection (EN IEC 60529)	IP68
Overload resistant	yes
Short-circuit protected	yes
Galvanic separation US/UA	yes

Mechanical data | Mounting data

Height	126 mm
Width	50 mm
Depth	34.5 mm
Suitable for mounting type	2-hole screw mounting

Environmental characteristics | Climatic

Operating temperature min.	-25 °C
Operating temperature max.	70 °C
Storage temperature min.	-40 °C
Storage temperature max.	85 °C

Conformity

Product standard	IEC/EN 61131-2
------------------	----------------

Connection type 3

Connection type 1	X0-X3
Connection type 2	X4-X7
Connection type 3	XZ1
Family construction form	M12
No. of poles	5
Coding	A
Gender	female
PIN 1	24 V DC UA
PIN 2	DIO (UA)
PIN 3	0 V UA
PIN 4	DIO (UA)
PIN 5	FE
Family construction form	M12
No. of poles	5
Coding	A
Gender	female
PIN 1	24 V DC US
PIN 2	DIO (US)
PIN 3	0 V US
PIN 4	DIO (US)
PIN 5	FE
Family construction form	M12
No. of poles	5
Coding	A
Gender	male
PIN 1	24 V DC (US) (L +)
PIN 2	24 V DC (UA) (P 24)
PIN 3	0 V (US) (L -)

PIN 4	C / Q / IO-Link
PIN 5	0 V (UA) (N 24)