

MIRO MULTI TIMER 24VDC-1S



MIRO MULTI-TIMER 24VDC-1S

Art.No.: 6652350
Weight: 0.04
Country of origin: CZ
Model designation: MIRO MULTI TIMER 24VDC-1S



Relay output
Impulse expansion: 0.1...300 s
Spring clamp terminals
safe separation (EN 60947-1)

Link to Product

Illustration



Time	+A1	Function
0.1...1.2 s	Out	Switch on delay
0.4...5 s	Out	One shot
3.5...40 s	Out	Modulation, pause starting
30...300 s	Load	Modulation, pulse starting
	B1	Switch off delay time
	Load	



Product may differ from Image



Header	
Material short text	MIRO MULTI TIMER 24VDC-1S
Commercial data	
URL Webshop	https://shop.murrelektronik.com/6652350
GTIN	4048879021906
ECLASS-6.0	27371790
ECLASS-6.1	27371790
ECLASS-7.0	27371790
ECLASS-7.1	27371790
ECLASS-8.0	27371605
ECLASS-8.1	27371605
ECLASS-9.0	27371605
ECLASS-9.1	27371605
ECLASS-10.0.1	27371605
ECLASS-10.1	27371605
ECLASS-11.0	27371605
ECLASS-11.1	27371605
ECLASS-12.0	27371605
ECLASS-13.0	27371605
ECLASS-14.0	27371605
ETIM-5.0	EC001439
ETIM-6.0	EC001439
ETIM-7.0	EC001439
ETIM-8.0	EC001439
customs tariff number	85364190
EAN	4048879021906
Packaging unit	1
Electrical data Input	
Input voltage DC	24 V
Input voltage DC min.	20.4 V
Input voltage DC max.	26.4 V
Input current	20 mA
Input current DC max.	16 mA

Control voltage DC	24 V
Control voltage DC min.	20.4 V
Control voltage DC max.	26.4 V
Control current	5 mA

Electrical data | Output

Output voltage adjustable	no
Output current max.	6 A
Switching voltage AC max.	250 V
Switching voltage DC max.	250 V
Switching current DC	100 mA
Switching frequency max.	10 Hz
Power rating AC max.	1,500 VA
Power rating DC max.	120 W

Device protection

Condition lifetime	load-dependent
--------------------	----------------

Device protection | Electrical

Electrical lifetime	0 cycles
Rated surge voltage	4 kV

Device protection | Mechanical

Mechanical endurance	0 cycles
----------------------	----------

Mechanical data

Response time max.	10 ms
Drop-out time max.	15 ms
Bounce time max.	1.5 ms

Mechanical data | Material data

Material contact	Ag Sn O2
------------------	----------

Mechanical data | Mounting data

Height	91 mm
Width	6.2 mm
Depth	70 mm
Mounting method	geschnappt
Suitable for mounting type	(EN 60715), mounting rail

Environmental characteristics | Climatic

Operating temperature min.	-25 °C
Operating temperature max.	60 °C

Connection type 5

Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	black
Connection	Spring clamp terminals FK
PIN 1	+ A 1
Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	black
Connection	Spring clamp terminals FK
PIN 1	18
Family construction form	terminal
No. of poles	1
Gender	female

Color contact carrier	black
Connection	Spring clamp terminals FK
PIN 1	17
Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	black
Connection	Spring clamp terminals FK
PIN 1	+ B 1
Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	black
Connection	Spring clamp terminals FK
PIN 1	- A 2