

MIRO 6.2 OPTO-COUPLER MODULE

IN: 53 VDC - OUT: 48 VDC / 6 A

Art.No.: 6652519

Weight: 0.03



Country of origin: CZ

Model designation: MIRO,TR,24VDC,24VDC,6A, FK

Transistor 6 A

24 V DC

Spring clamp terminals

[Link to Product](#)**Illustration**

Product may differ from Image

**Header**

Material short text

MIRO,TR,24VDC,24VDC,6A, FK

Commercial data

URL Webshop

<https://shop.murrelektronik.com/6652519>

GTIN	4048879021753
ECLASS-6.0	27371601
ECLASS-6.1	27371604
ECLASS-7.0	27371604
ECLASS-7.1	27371604
ECLASS-8.0	27371604
ECLASS-8.1	27371604
ECLASS-9.0	27371604
ECLASS-9.1	27371604
ECLASS-10.0.1	27371604
ECLASS-10.1	27371604
ECLASS-11.0	27371604
ECLASS-11.1	27371604
ECLASS-12.0	27371604
ECLASS-13.0	27371604
ECLASS-14.0	27371604
ETIM-5.0	EC001504
ETIM-6.0	EC001504
ETIM-7.0	EC001504
ETIM-8.0	EC001504
customs tariff number	85414900
EAN	4048879021753
Packaging unit	1
Electrical data Input	
Input voltage DC min.	10 V
Input voltage DC max.	53 V
Input voltage OFF DC min.	0 V
Input voltage OFF DC max.	5 V
Current input DC	10 mA
Electrical data Output	
Voltage drop DC max.	0.1 V
Quiescent current OFF max.	0.025 mA
Switch on delay max.	2 ms
Switch off delay max.	5 ms
Voltage switching DC min.	5 V
Switching voltage DC max.	48 V
Switching current min.	1 mA
Switching current max.	6 A
Switching frequency ohmic max.	1 Hz
Switching frequency inductive max.	0.1 Hz
Diagnostics	
Status indication LED	yellow
Device protection Electrical	
Rated insulation voltage	2,750 V
Device protection Media	
Flame resistance	flame retardant
Mechanical data Material data	
Material housing	Plastic
Color housing	black
Mechanical data Mounting data	
Height	78 mm

Width	6.2 mm
-------	--------

Depth	70 mm
-------	-------

Mounting method	geschnappt
-----------------	------------

Suitable for mounting type	(EN 60715), mounting rail
----------------------------	---------------------------

Environmental characteristics | Climatic

Operating temperature min.	-20 °C
----------------------------	--------

Operating temperature max.	60 °C
----------------------------	-------

Connection type 4

Family construction form	terminal
--------------------------	----------

No. of poles	1
--------------	---

Gender	female
--------	--------

Color contact carrier	black
-----------------------	-------

Connection	Spring clamp terminals FK
------------	---------------------------

PIN 1	13 +
-------	------

Family construction form	terminal
--------------------------	----------

No. of poles	1
--------------	---

Gender	female
--------	--------

Color contact carrier	black
-----------------------	-------

Connection	Spring clamp terminals FK
------------	---------------------------

PIN 1	14
-------	----

Family construction form	terminal
--------------------------	----------

No. of poles	1
--------------	---

Gender	female
--------	--------

Color contact carrier	black
-----------------------	-------

Connection	Spring clamp terminals FK
------------	---------------------------

PIN 1	+ A 1
-------	-------

Family construction form	terminal
--------------------------	----------

No. of poles	1
--------------	---

Gender	female
--------	--------

Color contact carrier	black
-----------------------	-------

Connection	Spring clamp terminals FK
------------	---------------------------

PIN 1	- A 2
-------	-------