

MIRO 6.2 24VDC 250VAC/DC-1A OPTO-COUPLER MODULE

IN: 53 VDC - OUT: 250 VAC / 350 VDC / 1 A

Art.No.: 6652572

Weight: 0.02

Country of origin: CZ



Model designation: MIRO6.2,24VDC,250VAC/DC-1A

Transistor 1 A


24 V DC

Spring clamp terminals

Multi voltage output

[Link to Product](#)**Illustration**

Product may differ from Image

**Header**

Material short text

MIRO6.2,24VDC,250VAC/DC-1A

Commercial data

URL Webshop	https://shop.murrelektronik.com/6652572
GTIN	4048879021661
ECLASS-6.0	27371601
ECLASS-6.1	27371604
ECLASS-7.0	27371604
ECLASS-7.1	27371604
ECLASS-8.0	27371604
ECLASS-8.1	27371604
ECLASS-9.0	27371604
ECLASS-9.1	27371604
ECLASS-10.0.1	27371604
ECLASS-10.1	27371604
ECLASS-11.0	27371604
ECLASS-11.1	27371604
ECLASS-12.0	27371604
ECLASS-13.0	27371604
ECLASS-14.0	27371604
ETIM-5.0	EC001504
ETIM-6.0	EC001504
ETIM-7.0	EC001504
ETIM-8.0	EC001504
customs tariff number	85414900
EAN	4048879021661
Packaging unit	1

Electrical data | Input

Input voltage DC min.	10 V
Input voltage DC max.	53 V
Input voltage OFF DC min.	0 V
Input voltage OFF DC max.	5 V
Current input DC	10 mA

Electrical data | Output

Voltage drop AC max.	0.7 V
Voltage drop DC max.	0.7 V
Quiescent current OFF max.	0.025 mA
Switch on delay max.	3 ms
Switch off delay max.	6 ms
Voltage switching AC min.	5 V
Switching voltage AC max.	250 V
Voltage switching DC min.	5 V
Switching voltage DC max.	350 V
Switching current min.	1 mA
Switching current max.	1 A
Switching frequency max.	10 Hz

Diagnostics

Status indication LED	yellow
-----------------------	--------

Device protection | Electrical

Rated insulation voltage	2,750 V
--------------------------	---------

Device protection | Media

Flame resistance	flame retardant
------------------	-----------------

Mechanical data | Material data

Material housing	Plastic
Color housing	black

Mechanical data Mounting data	
Height	78 mm
Width	62 mm
Depth	70 mm
Mounting method	geschnappt
Suitable for mounting type	(EN 60715), mounting rail
Environmental characteristics Climatic	
Operating temperature min.	-20 °C
Operating temperature max.	60 °C
Connection type 4	
Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	black
Connection	Spring clamp terminals FK
PIN 1	13
Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	black
Connection	Spring clamp terminals FK
PIN 1	14
Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	black
Connection	Spring clamp terminals FK
PIN 1	A 1
Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	black
Connection	Spring clamp terminals FK
PIN 1	A 2