

Reset button with 1 push button

In a IP65 enclosure

Art.No.: 69010

Weight: 0.103

Country of origin: DE

Model designation: R-Button 42 1NO M12(4)

R-Button / 42 1NO M12(4)

with M12 connection

4-pole

1 button (1 NO contact)

Delivery contents:




Flat lens, transparent clear, red, yellow, green, blue

Label plates, O, I, R

mounting with clip on the back side

Link to Product

Illustration



Product may differ from Image



Commercial data

The information in this Product-PDF has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2025-09-25

Murrelektronik GmbH | Grabenstraße 29 | 71570 Oppenweiler | Fon +49 (71 91) 47-0 | Fax +49 (71 91) 47-491000 | shop@murrelektronik.com | shop.murrelektronik.com

URL Webshop	https://shop.murrelektronik.com/69010
GTIN	4048879594288
ECLASS-6.0	27371228
ECLASS-6.1	27371228
ECLASS-7.0	27371228
ECLASS-7.1	27371228
ECLASS-8.0	27371228
ECLASS-8.1	27371228
ECLASS-9.0	27371228
ECLASS-9.1	27371228
ECLASS-10.0.1	27371228
ECLASS-10.1	27371228
ECLASS-11.0	27371228
ECLASS-11.1	27371228
ECLASS-12.0	27371228
ECLASS-13.0	27371228
ECLASS-14.0	27371228
ETIM-5.0	EC000225
ETIM-6.0	EC000225
ETIM-7.0	EC000225
ETIM-8.0	EC000225
EAN	4048879594288

Electrical data | Output

Switching current (AC-15)	15 A
Switching current (DC-13)	2.2 A
Utilization category AC-15 (EN IEC 60947-5-1)	1.5 A @ 240 V
Utilization category DC-13 (EN IEC 60947-5-1)	2 A @ 24 V

Device protection

Condition lifetime	load-dependent, temperature dependent
--------------------	---------------------------------------

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP65
Electrical lifetime	1,000,000 Cycles

Device protection | Mechanical

Mechanical endurance	1,000,000 Cycles
----------------------	------------------

Mechanical data

Bounce time max.	10 ms
------------------	-------

Mechanical data | Material data

Material contact	AgNi
------------------	------

Mechanical data | Mounting data

Height	29 mm
Width	124 mm
Depth	42 mm

Environmental characteristics | Climatic

Operating temperature min.	-25 °C
Operating temperature max.	70 °C
Storage temperature min.	-25 °C
Storage temperature max.	85 °C

Connection type 1

Family construction form	M12
No. of poles	4

Coding	A
Gender	male
Color contact carrier	black
PIN 1	NO
PIN 4	NO