



SCALANCE XC208 manageable Layer 2 IE switch; IEC 62443-4-2 certified; 8x 10/100 Mbit/s RJ45 ports; 1x console port; diagnostics LED; redundant power supply; temperature range -40 °C to +70 °C; assembly: DIN rail/S7 mounting rail/wall Office redundancy functions features (RSTP, VLAN,...); PROFINET IO device Ethernet/IP-compliant C-plug slot;

product type designation	
product brand name	SCALANCE
product type designation	XC208
Technical Product Detail Page	https://l.siemens.com/1P6GK5208-0BA00-2AC2
transfer rate	
transfer rate	10, 100 Mbit/s
interfaces / for communication / integrated	
number of electrical connections	
• for network components or terminal equipment	8; RJ45
number of 10/100 Mbit/s RJ45 ports	
• with securing collar	8
interfaces / other	
number of electrical connections	
• for operator console	1
• for signaling contact	1
• for power supply	1
design of the removable storage	
• C-PLUG	Yes
operating voltage / of the signaling contacts	
• at DC / rated value	24 V
operational current / of the signaling contacts	
• at DC / maximum	0.1 A
supply voltage, current consumption, power loss	
product component / connection for redundant voltage supply	Yes
type of voltage / 1 / of the supply voltage	
• supply voltage / 1 / rated value	24 V
• power loss [W] / 1 / rated value	4.2 W
• consumed current / 1 / at rated supply voltage / maximum	0.175 A
• consumed current / 1 / maximum	0.35 A
• product component / 1 / fusing at power supply input	Yes
ambient conditions	
ambient temperature	
• during operation	-40 ... +70 °C
• during storage	-40 ... +85 °C
• during transport	-40 ... +85 °C
relative humidity	
• at 25 °C / without condensation / during operation / maximum	95 %
protection class IP	IP20
design, dimensions and weights	

design	compact
width	60 mm
height	147 mm
depth	125 mm
net weight	0.52 kg
material / of the enclosure	Polycarbonate (PC-GF10) / pressure die cast aluminum
fastening method	
• 35 mm DIN-rail mounting	Yes
• wall mounting	Yes
• S7-300 rail mounting	Yes
• S7-1500 rail mounting	Yes
product features, product functions, product components / general	
cascading in the case of a redundant ring / at reconfiguration time of <1~0.31~s	50
cascading in cases of star topology	any (depending only on signal propagation time)
product function	
• QoS according to DSCP	Yes
product feature	
• Cut Through switching method	No
• Store & Forward switching method	Yes
product functions / management, configuration, engineering	
product function	
• CLI	Yes
• web-based management	Yes
• MIB support	Yes
• TRAPs via email	Yes
• configuration with STEP 7	Yes
• RMON	Yes
• SMTP server	No
• port mirroring	Yes
• multiport mirroring	Yes
• CoS	Yes
• PROFINET IO diagnosis	Yes
• switch-managed	Yes
PROFINET conformity class	B
telegram length / for Ethernet / maximum	1632 byte
protocol / is supported	
• Telnet	Yes
• HTTP	Yes
• HTTPS	Yes
• TFTP	Yes
• SFTP	Yes
• BOOTP	No
• GMRP	Yes
• DCP	Yes
• LLDP	Yes
• EtherNet/IP	Yes
• SNMP v1	Yes
• SNMP v2	Yes
• SNMP v3	Yes
• IGMP (snooping/querier)	Yes
identification & maintenance function	
• I&M0 - device-specific information	Yes
• I&M1 - higher level designation/location designation	Yes
product functions / diagnostics	
product function	
• port diagnostics	Yes
• statistics Packet Size	Yes
• statistics packet type	Yes
• error statistics	Yes
• SysLog	Yes

product functions / VLAN

product function	
• VLAN - port based	Yes
• VLAN - protocol-based	No
• VLAN - IP-based	No
number of VLANs / maximum	257
number of VLANs - dynamic / maximum	257
number of VLANs / at ring redundancy (HRP; MRP; standby link)	257

product functions / DHCP

product function	
• DHCP server	Yes
• DHCP client	Yes
• DHCP Option 82	Yes
• DHCP Option 66	Yes
• DHCP Option 67	Yes

product functions / redundancy

protocol / is supported / Media Redundancy Protocol (MRP)	Yes
product function	
• media redundancy protocol (MRP) with redundancy manager	Yes
• Media Redundancy Protocol Interconnection (MRP-I)	Yes
• of the PROFINET IO device / is supported / H-Sync forwarding	Yes
• of the PROFINET IO device / is supported / PROFINET system redundancy	Yes
• ring redundancy	Yes
• high speed redundancy protocol (HRP) with redundancy manager	Yes
• high speed redundancy protocol (HRP) with standby redundancy	Yes
• redundancy procedure STP	Yes
• redundancy procedure RSTP	Yes
• redundancy procedure RSTP+	Yes
• redundancy procedure MSTP	Yes
• Parallel Redundancy Protocol (PRP)/operation in the PRP-network	Yes
• Parallel Redundancy Protocol (PRP)/Redundant Network Access (RNA)	No
• passive listening	Yes
protocol / is supported	
• LACP	Yes

system modification during operation

product function / configuration in RUN via CiR/H-CiR	Yes
---	-----

product functions / security

product function	
• IEEE 802.1x (radius)	Yes
• RADIUS client	Yes
• broadcast/multicast/unicast limiter	Yes
• broadcast blocking	Yes
protocol / is supported	
• SSH	Yes
• SSL	Yes

product functions / time

product function	
• SICLOCK support	Yes
• NTP-client	Yes
• SNTP client	Yes
protocol / is supported	
• NTP	Yes
• SNTP	Yes

standards, specifications, approvals

certificate of suitability	
----------------------------	--

<ul style="list-style-type: none"> • CE marking • cULus approval • KC approval • Regulatory Compliance Mark (RCM) 	Yes Yes Yes Yes
product conformity / according to EMC-guideline	2014/30/EU
standard <ul style="list-style-type: none"> • for EMC interference emission • for immunity to EMC • for safety / from CSA and UL 	EN 61000-6-4, EN 50121-4 EN 61000-6-2, EN 50121-4 UL 60950-1 E115352
standards, specifications, approvals / hazardous environments	
certificate of suitability <ul style="list-style-type: none"> • ATEX • UKEX • IECEx • ULhazloc approval • CCC / for hazardous zone according to GB standard • FM registration 	Yes Yes Yes Yes Yes Yes
standards, specifications, approvals / other	
certificate of suitability <ul style="list-style-type: none"> • railway application in accordance with EN 50121-4 • RoHS conformity 	Yes Yes
IT security for industrial automation systems / according to IEC 62443-4-2:2019	Yes
standards, specifications, approvals / marine classification	
Marine classification association <ul style="list-style-type: none"> • American Bureau of Shipping Europe Ltd. (ABS) • French marine classification society (BV) • Chinese Classification Society (CCS) • Det Norske Veritas (DNV) • Korean Register of Shipping (KRS) • Lloyds Register of Shipping (LRS) • Nippon Kaiji Kyokai (NK) • Polski Rejestr Statkow (PRS) • Royal Institution of Naval Architects (RINA) 	No No No Yes No No Yes No Yes
standards, specifications, approvals / Environmental Product Declaration	
Environmental Product Declaration	Yes
global warming potential [CO2 eq] <ul style="list-style-type: none"> • total • during manufacturing • during operation • after end of life 	135.7 kg 26.3 kg 109 kg 0.4 kg
product functions / general	
MTBF	48 a
warranty period	5 a
product function / is supported / identification link	Yes; acc. to IEC 61406-1:2022
further information / internet links	
internet link <ul style="list-style-type: none"> • to website: Selection guide for cables and connectors • to web page: selection aid TIA Selection Tool • to website: Industrial communication • to web page: SiePortal • to website: Image database • to website: CAX-Download-Manager • to website: Industry Online Support 	https://support.industry.siemens.com/cs/ww/en/view/109766358 https://www.siemens.com/tstcloud https://www.siemens.com/simatic-net https://sieportal.siemens.com/ https://www.automation.siemens.com/blddb https://www.siemens.com/cax https://support.industry.siemens.com
security information	
security information	Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement – and continuously maintain – a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected

to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry. Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under <https://www.siemens.com/cert>. (V4.7)

Approvals / Certificates

General Product Approval



[Declaration of Con-
formity](#)



[China RoHS](#)



General Product Approval	EMV	For use in hazardous locations
--------------------------	-----	--------------------------------

[Declaration of Con-
formity](#)



[TUEV](#)

[KC](#)



For use in hazardous locations	Test Certificates	Maritime application
--------------------------------	-------------------	----------------------

[FM](#)

[CCC-Ex](#)

[Type Test Certific-
ates/Test Report](#)

[Special Test Certific-
ate](#)



Maritime application	Environment
----------------------	-------------



[NK / Nippon Kaiji Ky-
okai](#)



Industrial Communication

[PROFINET](#)

last modified: 10/28/2025