

M8 male 90° A-cod. solder pins



4-pol., 0.25mm², 3,5 - 5mm

Art.No.: 7000-08461-0000000  
Weight: 0.008  
Country of origin: DE  
Model designation: MSI-T


Male 90°  
M8, 4-pole  
with solder pins  
Connection cross section: max. 0.25 mm²

Link to Product

Illustration



Product may differ from Image



Side 1

|                                     |      |
|-------------------------------------|------|
| Family construction form            | M8   |
| Degree of protection (EN IEC 60529) | IP67 |

Commercial data

|            |          |
|------------|----------|
| ECLASS-6.0 | 27279221 |
| ECLASS-7.0 | 27440104 |
| ECLASS-8.0 | 27440104 |
| ECLASS-9.0 | 27440102 |

|                       |               |
|-----------------------|---------------|
| ECLASS-10.1           | 27440102      |
| ECLASS-11.1           | 27440102      |
| ECLASS-12.0           | 27440116      |
| ETIM-5.0              | EC001855      |
| customs tariff number | 85366990      |
| customs tariff number | 85366990      |
| GTIN                  | 4048879224635 |
| GTIN                  | 4048879224635 |
| Packaging unit        | 1             |
| Packaging unit        | 1             |

#### Electrical data | Supply

|                                    |      |
|------------------------------------|------|
| Operating voltage AC max.          | 30 V |
| Operating voltage DC max.          | 30 V |
| Current operating per contact max. | 4 A  |

#### Installation

|                               |                           |
|-------------------------------|---------------------------|
| Connection cross section max. | 0,25 mm <sup>2</sup>      |
| Rotation option               | 90° (4 outlet directions) |

#### Device protection | Electrical

|                                        |                   |
|----------------------------------------|-------------------|
| Additional condition protection degree | inserted, screwed |
|----------------------------------------|-------------------|

#### Mechanical data | Mounting data

|                     |         |
|---------------------|---------|
| Clamping range min. | 3,5 mm  |
| Clamping range max. | 5 mm    |
| Height              | 34,5 mm |
| Width               | 18,5 mm |
| Depth               | 12 mm   |

#### Environmental characteristics | Climatic

|                            |        |
|----------------------------|--------|
| Operating temperature min. | -25 °C |
| Operating temperature max. | 85 °C  |

#### Important installation notes

|                        |                                                                                                                                                       |
|------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|
| Note on strain relief  | Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.                                                   |
| Note on bending radius | <b>Attention:</b> Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces. |