



SIMATIC ET 200SP, Digital output module, DQ 16x 24V DC/0.5A Standard, Source output (PNP,P-switching) Packing unit: 1 piece, fits to BU-type A0, Colour Code CC00, substitute value output, module diagnostics for: short-circuit to L+ and ground, wire break, supply voltage

General information	
Product type designation	DQ 16x24VDC/0.5 ST
HW functional status	from FS21
Firmware version	V0.0
• FW update possible	No
usable BaseUnits	BU type A0
Color code for module-specific color identification plate	CC00
Product function	
• I&M data	Yes; I&M0 to I&M3
• Isochronous mode	No
Engineering with	
• STEP 7 TIA Portal configurable/integrated from version	STEP 7 TIA V14 with HSP0222 / integrated as of TIA V15
• STEP 7 configurable/integrated from version	V5.5 SP3 with HSP0230 V7.0 / integrated as of V5.6 SP1
• PCS 7 configurable/integrated from version	V8.1 SP1
• PROFIBUS from GSD version/GSD revision	One GSD file each, Revision 3 and 5 and higher
• PROFINET from GSD version/GSD revision	GSDML V2.3
Operating mode	
• DQ	Yes
• DQ with energy-saving function	No
• PWM	No
• Oversampling	No
• MSO	No
Supply voltage	
Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes
Input current	
Current consumption, max.	30 mA; without load
Output voltage	
Rated value (DC)	24 V
Power loss	
Power loss, typ.	1 W
Address area	
Address space per module	
• Address space per module, max.	2 byte; + 2 bytes for QI information
Hardware configuration	
Automatic encoding	Yes
• Mechanical coding element	Yes

• Type of mechanical coding element	Type A
Selection of BaseUnit for connection variants	
• 1-wire connection	BU type A0
• 2-wire connection	BU type A0 with AUX terminals or potential distributor module
• 3-wire connection	BU type A0 with AUX terminals or potential distributor module
Digital outputs	
Type of digital output	Source output (PNP, current-sourcing)
Number of digital outputs	16
Current-sinking	No
Current-sourcing	Yes
Digital outputs, parameterizable	Yes
output type acc. to IEC 61131, type 0.5	Yes
Short-circuit protection	Yes; Electronic
• Response threshold, typ.	1 A; 0.7 to 1.3 A
Open-circuit detection	Yes
Limitation of inductive shutdown voltage to	Typ. L+ (-50 V)
Controlling a digital input	Yes
Switching capacity of the outputs	
• with resistive load, max.	0.5 A
• with inductive load, max.	0.5 A
• on lamp load, max.	5 W
Load resistance range	
• lower limit	48 Ω
• upper limit	12 kΩ
Output current	
• for signal "1" rated value	0.5 A
• for signal "1" permissible range, max.	0.5 A
• for signal "0" residual current, max.	0.1 mA
Output delay with resistive load	
• "0" to "1", typ.	50 μs
• "1" to "0", typ.	100 μs
Parallel switching of two outputs	
• for uprating	No
• for redundant control of a load	Yes
Switching frequency	
• with resistive load, max.	100 Hz
• with inductive load, max.	0.1 Hz; higher frequencies are possible, see Equipment Manual "Maximum permitted switching frequency of inductive loads"
• on lamp load, max.	10 Hz
Total current of the outputs	
• Current per channel, max.	0.5 A
• Current per module, max.	8 A; see Equipment Manual "Derating curve"
Total current of the outputs (per module)	
horizontal installation	
— up to 40 °C, max.	8 A
— up to 50 °C, max.	6 A
— up to 60 °C, max.	4 A
vertical installation	
— up to 30 °C, max.	8 A
— up to 40 °C, max.	6 A
— up to 50 °C, max.	4 A
Cable length	
• shielded, max.	1 000 m
• unshielded, max.	600 m
Interrupts/diagnostics/status information	
Diagnostics function	Yes
Substitute values connectable	Yes
Alarms	
• Diagnostic alarm	Yes

Diagnoses			
Monitoring the supply voltage		Yes	
Wire-break		Yes; Module-wise	
Short-circuit to M		Yes; Module-wise	
Short-circuit to L+		Yes; Module-wise	
Group error		Yes	
Diagnostics indication LED			
Monitoring of the supply voltage (PWR-LED)		Yes; green PWR LED	
Channel status display		Yes; green LED	
for channel diagnostics		No	
for module diagnostics		Yes; green/red DIAG LED	
Potential separation			
Potential separation channels			
between the channels		No	
between the channels and backplane bus		Yes	
Between the channels and load voltage L+		No	
Isolation			
Isolation tested with		707 V DC (type test)	
Standards, approvals, certificates			
Suitable for safety functions		No	
Suitable for safety-related tripping of standard modules		No	
Ecological footprint			
environmental product declaration		Yes	
Global warming potential			
— global warming potential, (total) [CO2 eq]		29.3 kg	
— global warming potential, (during production) [CO2 eq]		3.98 kg	
— global warming potential, (during operation) [CO2 eq]		25.6 kg	
— global warming potential, (after end of life cycle) [CO2 eq]		-0.245 kg	
Ambient conditions			
Ambient temperature during operation			
horizontal installation, min.		-30 °C; < 0 °C as of FS03	
horizontal installation, max.		60 °C	
vertical installation, min.		-30 °C; < 0 °C as of FS03	
vertical installation, max.		50 °C	
Altitude during operation relating to sea level			
Installation altitude above sea level, max.		5 000 m; restrictions for installation altitudes > 2 000 m, see ET 200SP system manual	
Dimensions			
Width		15 mm	
Height		73 mm	
Depth		58 mm	
Weights			
Weight, approx.		30 g	
Classifications			
		Version	Classification
	eClass	14	27-24-26-04
	eClass	12	27-24-26-04
	eClass	9.1	27-24-26-04
	eClass	9	27-24-26-04
	eClass	8	27-24-26-04
	eClass	7.1	27-24-26-04
	eClass	6	27-24-26-04
	ETIM	10	EC001599
	ETIM	9	EC001599
	ETIM	8	EC001599

ETIM	7	EC001599
IDEA	4	3566
UNSPSC	15	32-15-17-05

Approvals / Certificates

General Product Approval



[Miscellaneous](#)

[Manufacturer Declaration](#)

[KC](#)



General Product Approval	EMV	For use in hazardous locations
--------------------------	-----	--------------------------------

[KC](#)



[KC](#)



[CCC-Ex](#)

[FM](#)

For use in hazardous locations	Maritime application
--------------------------------	----------------------



[Miscellaneous](#)

[Type Examination Certificate](#)



Maritime application



[NK / Nippon Kaiji Kyokai](#)



[CCS \(China Classification Society\)](#)

Maritime application	Environment
----------------------	-------------



last modified: 10/23/2025