



communication module PROFIBUS

product brand name	SIRIUS		
product category	Communication modules		
product designation	Communication module		
design of the product	PROFIBUS		
product type designation	3RW59		
manufacturer's article number of soft starter	3RW50 3RW51 3RW52 3RW55		
General technical data			
reference code according to IEC 81346-2	A		
Substance Prohibitance (Date)	02/15/2018		
SVHC substance name	Lead - 7439-92-1 Lead monoxide (lead oxide) - 1317-36-8		
Net Weight	0.133 kg		
Installation/ mounting/ dimensions			
mounting position	any		
fastening method	screw fixing		
height	126 mm		
width	28 mm		
depth	82 mm		
weight without packaging	0.1 kg		
Ambient conditions			
installation altitude at height above sea level maximum	5 000 m		
ambient temperature	- during operation-25 ... +60 °C; observe derating of basic unit above 40 °C - during storage and transport-40 ... +80 °C		
environmental category	- during operation according to IEC 607213K6 (no ice formation, only occasional condensation), 3C3 (no salt mist), 3S2 (sand must not get into the devices), 3M6 - during storage according to IEC 607211K6 (only occasional condensation), 1C2 (no salt mist), 1S2 (sand must not get inside the devices), 1M4 - during transport according to IEC 607212K2, 2C1, 2S1, 2M2 (max. height of fall 0.8 m)		
Electrical Safety			
protection class IP on the front according to IEC 60529	IP20		
touch protection on the front according to IEC 60529	finger-safe, for vertical contact from the front		
Approvals Certificates			
General Product Approval		EMV	For use in hazard-ous locations



[Miscellaneous](#)

Test Certificates

Maritime application

[Type Test Certificates/Test Report](#)



other

Environment

Industrial Communication

[Confirmation](#)

[Environmental Confirmations](#)



Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RW5980-0CP00>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RW5980-0CP00>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RW5980-0CP00&lang=en

Cax online generator

<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RW5980-0CP00>

Characteristic curves

https://curves.simaris.siemens.com/curves/<mmp_prod_noCOMP='HAUPT'></mmp_prod_no>

Characteristic: Tripping characteristics, I²t, Let-through current


<https://support.industry.siemens.com/cs/ww/en/ps/3RW5980-0CP00/char>

Characteristic: Installation altitude


https://www.automation.siemens.com/bilddb/index.aspx?gridview=view2&objkey=G_NSB0_XX_01704&showdetail=true&view=Search

Simulation Tool for Soft Starters (STS)

<https://support.industry.siemens.com/cs/ww/en/view/101494917>



-A



-X31

PROFIBUS DP

-X1:DP

