



circuit breaker 3VA5 UL Frame 125 breaking capacity class S 25 kA @ 277 V 1-pole, line protection TM210, FTFM,  $I_n=25$  A overload protection  $I_r=25$  A permanently set short-circuit protection  $I_i=12 \times I_n$  without connection

| Model                                                                                                                      |                             |
|----------------------------------------------------------------------------------------------------------------------------|-----------------------------|
| product brand name                                                                                                         | SENTRON                     |
| product designation                                                                                                        | Molded-case circuit breaker |
| product designation / according to UL file                                                                                 | SEAS                        |
| design of the product                                                                                                      | System protection           |
| design of the load switch / according to UL 489 / Heating, Air Conditioning, and Refrigeration circuit breaker (HACR Type) | Yes                         |
| design of the load switch / according to UL 489 / High-Intensity-Discharge circuit breaker (HID Type)                      | Yes                         |
| design of the load switch / according to UL 489 / Switching Duty circuit breaker (SWD Type)                                | No                          |
| design of the overcurrent release                                                                                          | TM210                       |
| protection function of the overcurrent release                                                                             | LI                          |
| number of poles                                                                                                            | 1                           |
| General technical data                                                                                                     |                             |
| insulation voltage / rated value                                                                                           | 500 V                       |
| operating voltage / at DC / rated value                                                                                    | 125 V                       |
| operating voltage / at AC / rated value                                                                                    | 415 V                       |
| power loss [W] / maximum                                                                                                   | 2.87 W                      |
| power loss [W] / for rated value of the current / at AC / in hot operating state / per pole                                | 2.87 W                      |
| mechanical service life (operating cycles) / typical                                                                       | 20 000                      |
| electrical endurance (operating cycles) / at AC-1 / at 380/415 V                                                           | 8 000                       |
| electrical endurance (operating cycles) / at AC-1 / at 690 V                                                               | 4 000                       |
| electrical endurance (operating cycles) / at 480 V                                                                         | 8 000                       |
| electrical endurance (operating cycles) / at 600 V                                                                         | 4 000                       |
| product feature / for neutral conductors / upgradable/retrofitable / short-circuit and overload proof                      | No                          |
| product function                                                                                                           |                             |
| • communication function                                                                                                   | No                          |
| • other measurement function                                                                                               | No                          |
| Net Weight                                                                                                                 | 380 g                       |
| Current                                                                                                                    |                             |
| marking / according to UL 489 / 100%-rated breaker                                                                         | No                          |
| operational current                                                                                                        |                             |
| • at 40 °C                                                                                                                 | 25 A                        |
| • at 45 °C                                                                                                                 | 24 A                        |
| • at 50 °C                                                                                                                 | 24 A                        |
| • at 55 °C                                                                                                                 | 23 A                        |
| • at 60 °C                                                                                                                 | 23 A                        |

|                                                                                                                               |                                                                                                                                                                |
|-------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <ul style="list-style-type: none"> <li>• at 65 °C</li> <li>• at 70 °C</li> </ul>                                              | 23 A<br>22 A                                                                                                                                                   |
| <b>Switching capacity according to IEC 60947</b>                                                                              |                                                                                                                                                                |
| switching capacity class of the circuit breaker                                                                               | S                                                                                                                                                              |
| maximum short-circuit current breaking capacity (I <sub>cu</sub> )                                                            |                                                                                                                                                                |
| <ul style="list-style-type: none"> <li>• at 240 V</li> <li>• at 415 V</li> </ul>                                              | 25 kA<br>5 kA                                                                                                                                                  |
| operating short-circuit current breaking capacity (I <sub>cs</sub> )                                                          |                                                                                                                                                                |
| <ul style="list-style-type: none"> <li>• at 240 V</li> <li>• at 415 V</li> </ul>                                              | 25 kA<br>5 kA                                                                                                                                                  |
| short-circuit current making capacity (I <sub>cm</sub> )                                                                      |                                                                                                                                                                |
| <ul style="list-style-type: none"> <li>• at 240 V</li> <li>• at 415 V</li> </ul>                                              | 52.5 kA<br>7.5 kA                                                                                                                                              |
| design of short-circuit protection                                                                                            | For switching power values in DC networks, see the 3VA molded case circuit breaker device manual; link to be found under Service & Support in the last chapter |
| <b>Switching capacity according to UL 489</b>                                                                                 |                                                                                                                                                                |
| current breaking capacity                                                                                                     |                                                                                                                                                                |
| <ul style="list-style-type: none"> <li>• at 120 V</li> <li>• at 277 V</li> <li>• at 347 V</li> </ul>                          | 65 kA<br>25 kA<br>14 kA                                                                                                                                        |
| <b>Adjustable parameters</b>                                                                                                  |                                                                                                                                                                |
| adjustable response value setting current (I <sub>r</sub> ) / of the L-trip / with I <sub>2t</sub> characteristic             |                                                                                                                                                                |
| <ul style="list-style-type: none"> <li>• minimum</li> <li>• maximum</li> </ul>                                                | 25 A<br>25 A                                                                                                                                                   |
| adjustable response value delay time (t <sub>r</sub> ) / for L-tripping / with I <sub>2t</sub> characteristic                 |                                                                                                                                                                |
| <ul style="list-style-type: none"> <li>• minimum</li> <li>• maximum</li> </ul>                                                | 1 s<br>1 s                                                                                                                                                     |
| adjustable response value setting current (I <sub>i</sub> ) / for I-tripping                                                  |                                                                                                                                                                |
| <ul style="list-style-type: none"> <li>• minimum</li> <li>• maximum</li> </ul>                                                | 300 A<br>300 A                                                                                                                                                 |
| adjustable setting current (I <sub>nN</sub> ) / for N-tripping                                                                |                                                                                                                                                                |
| <ul style="list-style-type: none"> <li>• minimum</li> <li>• maximum</li> </ul>                                                | 0 A<br>0 A                                                                                                                                                     |
| product function / grounding protection                                                                                       | No                                                                                                                                                             |
| <b>Mechanical Design</b>                                                                                                      |                                                                                                                                                                |
| product component                                                                                                             |                                                                                                                                                                |
| <ul style="list-style-type: none"> <li>• undervoltage release</li> <li>• voltage trigger</li> <li>• trip indicator</li> </ul> | No<br>No<br>No                                                                                                                                                 |
| height [in]                                                                                                                   | 5.51 in                                                                                                                                                        |
| height                                                                                                                        | 140 mm                                                                                                                                                         |
| width [in]                                                                                                                    | 1 in                                                                                                                                                           |
| width                                                                                                                         | 25.4 mm                                                                                                                                                        |
| depth [in]                                                                                                                    | 3.01 in                                                                                                                                                        |
| depth                                                                                                                         | 76.5 mm                                                                                                                                                        |
| <b>Connections</b>                                                                                                            |                                                                                                                                                                |
| arrangement of electrical connectors / for main current circuit                                                               | Without connection                                                                                                                                             |
| type of electrical connection / for main current circuit                                                                      | Without                                                                                                                                                        |
| <b>Auxiliary circuit</b>                                                                                                      |                                                                                                                                                                |
| number of CO contacts / for auxiliary contacts                                                                                | 0                                                                                                                                                              |
| <b>Accessories</b>                                                                                                            |                                                                                                                                                                |
| product extension / optional / motor drive                                                                                    | No                                                                                                                                                             |
| <b>Environmental conditions</b>                                                                                               |                                                                                                                                                                |
| protection class IP / on the front                                                                                            | IP40                                                                                                                                                           |
| ambient temperature                                                                                                           |                                                                                                                                                                |
| <ul style="list-style-type: none"> <li>• during operation / minimum</li> <li>• during operation / maximum</li> </ul>          | -25 °C<br>70 °C                                                                                                                                                |

- during storage / minimum
- during storage / maximum

-40 °C

80 °C

reference code / according to IEC 81346-2

Q

## Approvals / Certificates

### General Product Approval



[Confirmation](#)



### General Product Approval

### EMV



[Miscellaneous](#)



### Test Certificates

### Maritime application

[Special Test Certificate](#)

[Type Test Certificates/Test Report](#)



### Maritime application

### other

### Environment



[Confirmation](#)

[Miscellaneous](#)

[Environmental Confirmations](#)

## Further information

### Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

### Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

### Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/lowvoltage/catalogs>

### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA5125-4ED11-0AA0>

### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3VA5125-4ED11-0AA0>

### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[https://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3VA5125-4ED11-0AA0](https://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA5125-4ED11-0AA0)

### CAX-Online-Generator



<https://www.siemens.com/cax>


### Tender specifications

<https://www.siemens.com/specifications>

### Characteristic curves

[https://curves.simaris.siemens.com/curves/<mmp\\_prod\\_noCOMP='HAUPT'></mmp\\_prod\\_no>](https://curves.simaris.siemens.com/curves/<mmp_prod_noCOMP='HAUPT'></mmp_prod_no>)





last modified:

4/4/2025 

