

MVP12-V, 8XM12, 4POLE, M23 12POL. CON.

Connector exit frontside

Art.No.: 27765

Weight: 0.131

Country of origin: DE

Model designation: MVB8-V

8-way, 4-pole




M23 plug connection


12-pole used

with LED for digital PNP-signals 24 V DC

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)**Illustration**



Product may differ from Image



Commercial data	
URL Webshop	https://shop.murrelektronik.com/27765
GTIN	4048879063371
ECLASS-6.0	27279219
ECLASS-6.1	27279219
ECLASS-7.0	27279219
ECLASS-7.1	27279219
ECLASS-8.0	27279219
ECLASS-8.1	27279219
ECLASS-9.0	27440111
ECLASS-10.0.1	27440111
ECLASS-10.1	27440111
ECLASS-11.0	27440111
ECLASS-11.1	27440111
ECLASS-12.0	27440111
ECLASS-13.0	27440111
ECLASS-14.0	27440111
ETIM-5.0	EC002585
ETIM-6.0	EC002585
ETIM-7.0	EC002585
ETIM-8.0	EC002585
EAN	4048879063371
customs tariff number	85366990
customs tariff number	85366990
EAN	4048879063371
EAN	4048879063371
Packaging unit	1
Packaging unit	1
Electrical data Supply	
Operating voltage DC	24 V
Current operating per contact max.	4 A
Total current max.	10 A
Industrial communication	

Number of signals per port 1

Installation | Connection

Mounting set M12 x 1

Device protection | Electrical

Degree of protection (EN IEC 60529) IP67

Additional condition protection degree mounted, screwed

Device protection | Media

Flame resistance flame retardant

Mechanical data | Material data

Material housing Plastic

Mechanical data | Mounting data

Height 149.2 mm

Width 50.2 mm

Depth 16.5 mm

Mounting method Schraubgewinde

Environmental characteristics | Climatic

Operating temperature min. -20 °C

Operating temperature max. 80 °C

Connection type 1

Family construction form M23

No. of poles 12

Coding A

Gender male

Color contact carrier black

PIN 1 WH

PIN 2 GN

PIN 3 YE

PIN 4 GY

PIN 5 PK

PIN 6 RD

PIN 7 BK

PIN 8 VT

PIN 9 BU

PIN 10 BU

PIN 11 BN

PIN 12 YE / GN