

MODLINK MSDD FRAME DBL METAL

Nickeled

Art.No.: 4000-68123-0000000

Weight: 0.628

Country of origin: CN

Model designation: Rahmenmodul 2-fach IP65 matt vernickelt

Frame: metal, matte nickel plated


Lid: metal, matte nickel plated

Link to Product

Illustration



Product may differ from Image



0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0

[illegible]

Header

Material short text	Rahmenmodul 2-fach IP65 matt vernickelt
---------------------	---

Commercial data

URL Webshop	https://shop.murrelektronik.com/4000-68123-0000000
GTIN	4048879035286

ECLASS-6.0	27189217
ECLASS-6.1	27189260
ECLASS-7.0	27189260
ECLASS-7.1	27189260
ECLASS-8.0	27189260
ECLASS-8.1	27189260
ECLASS-9.0	27182810
ECLASS-9.1	27189260
ECLASS-10.0.1	27182810
ECLASS-10.1	27182810
ECLASS-11.0	27182810
ECLASS-11.1	27182810
ECLASS-12.0	27182810
ECLASS-13.0	27182810
ECLASS-14.0	27182810
ETIM-5.0	EC002625
ETIM-6.0	EC002625
ETIM-7.0	EC002625
ETIM-8.0	EC002625
customs tariff number	85389099
EAN	4048879035286
Packaging unit	1

Device protection

Shielded	yes
----------	-----

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP65
-------------------------------------	------

Mechanical data | Material data

Material housing	Fine zinc die casting
Coating housing	surface finished

Mechanical data | Mounting data

Height	120 mm
Width	130 mm
Depth	35 mm
Suitable for installation wall thickness min.	1 mm
Suitable for installation wall thickness max.	5 mm

Environmental characteristics | Climatic

Operating temperature min.	-10 °C
Operating temperature max.	60 °C
Storage temperature min.	-25 °C
Storage temperature max.	60 °C

Frame

Material housing	Fine zinc die casting
Coating housing	surface finished
Suitable for installation wall thickness min.	1 mm
Suitable for installation wall thickness max.	5 mm
Degree of protection (EN IEC 60529)	IP65
Operating temperature min.	-10 °C
Operating temperature max.	60 °C
Storage temperature min.	-25 °C