

RMMDH-AK 11/24 WITH TOGGLE SWITCH

IN: 24 VDC - OUT: 250 VAC/DC / 3 A

Art.No.: 51101

Weight: 0.043

Country of origin: CZ

Model designation: RMMDH-AK 11/24 VDC



1 relay; 1 NO contact

3 A

24 V DC

with minus plug link

Toggle switch for bridging the NO contact

[Link to Product](#)
Illustration


Product may differ from Image


Header

Material short text

RMMDH-AK 11/24 VDC

Commercial data

The information in this Product-PDF has been compiled with the utmost care.
 Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2025-10-05

Murrelektronik GmbH | Grabenstraße 29 | 71570 Oppenweiler | Fon +49 (71 91) 47-0 | Fax +49 (71 91) 47-491000 | shop@murrelektronik.com | shop.murrelektronik.com

URL Webshop	https://shop.murrelektronik.com/51101
GTIN	4048879027809
Scope of delivery	Jumper (Art-No. 90960)
ECLASS-6.0	27371001
ECLASS-6.1	27371601
ECLASS-7.0	27371601
ECLASS-7.1	27371601
ECLASS-8.0	27371601
ECLASS-8.1	27371601
ECLASS-9.0	27371601
ECLASS-9.1	27371601
ECLASS-10.0.1	27371601
ECLASS-10.1	27371601
ECLASS-11.0	27371601
ECLASS-11.1	27371601
ECLASS-12.0	27371601
ECLASS-13.0	27371601
ECLASS-14.0	27371601
ETIM-5.0	EC001437
ETIM-6.0	EC001437
ETIM-7.0	EC001437
ETIM-8.0	EC001437
customs tariff number	85364900
EAN	4048879027809
Packaging unit	1

Electrical data | Input

Input voltage DC	24 V
Input voltage DC min.	19.2 V
Input voltage DC max.	28 V
Input current	10 mA

Electrical data | Output

Switching voltage AC max.	250 V
Switching voltage DC max.	250 V
Switching current max.	3 A
Switching current DC	100 mA
Switching frequency max.	15 Hz
Power rating AC max.	750 VA
Power rating DC max.	90 W
Switching capacity AC-12 (EN IEC 60947-5-1)	3 A (24/110/230 V AC)
Utilization category AC-15 (EN IEC 60947-5-1)	3 A @ 24 V 3 A @ 110 V 3 A @ 230 V
Utilization category DC-13 (EN IEC 60947-5-1)	1.5 A @ 24 V 0.3 A @ 110 V 0.15 A @ 230 V

Diagnostics

Status indication LED	red
-----------------------	-----

Device protection

Condition lifetime	load-dependent
--------------------	----------------

Device protection | Electrical

Electrical lifetime	0 cycles
Rated surge voltage	3 kV

Device protection | Mechanical

Mechanical endurance	0 cycles
----------------------	----------

Mechanical data

Response time max.	10 ms
Drop-out time max.	10 ms
Bounce time max.	2 ms

Mechanical data | Material data

Material contact	Ag Cd 0
------------------	---------

Mechanical data | Mounting data

Height	82 mm
Width	12 mm
Depth	68 mm
Mounting method	geschnappt
Suitable for mounting type	Mounting rail TH35, (EN 60715), G32

Environmental characteristics | Climatic

Operating temperature min.	-20 °C
Operating temperature max.	50 °C

Connection type 3

Family construction form	terminal
No. of poles	2
Gender	female
Connection	Screw terminals SK
PIN 1	+ A 1
PIN 2	- A 2
Family construction form	terminal
No. of poles	2
Gender	female
Connection	Screw terminals SK
PIN 1	13
PIN 2	13
Family construction form	terminal
No. of poles	2
Gender	female
Connection	Screw terminals SK
PIN 1	14
PIN 2	14