

RMME 11/230 AC INPUT RELAY

to be discontinued - Last Time Order: 2024-10-31

Art.No.: 51517

Weight: 0.027

Country of origin: CZ



Model designation: MME 11/230 AC

1 relay; 1 NO contact

1 A

230 V AC

Screw terminals

Link to Product**Illustration**

Product may differ from Image

**Commercial data**

URL Webshop

<https://shop.murrelektronik.com/51517>

GTIN

4048879027540

ECLASS-6.0	27371001
ECLASS-6.1	27371601
ECLASS-7.0	27371601
ECLASS-7.1	27371601
ECLASS-8.0	27371601
ECLASS-8.1	27371601
ECLASS-9.0	27371601
ECLASS-9.1	27371601
ECLASS-10.0.1	27371601
ECLASS-10.1	27371601
ECLASS-11.0	27371601
ECLASS-11.1	27371601
ECLASS-12.0	27371601
ECLASS-13.0	27371601
ECLASS-14.0	27371601
ETIM-5.0	EC001437
ETIM-6.0	EC001437
ETIM-7.0	EC001437
ETIM-8.0	EC001437
EAN	4048879027540

Electrical data | Input

Input voltage AC	230 V
Input voltage AC min.	195 V
Input voltage AC max.	253 V
Input voltage DC	230 V
Input voltage DC min.	195 V
Input voltage DC max.	253 V
Input current	6 mA

Electrical data | Output

Switching voltage AC max.	125 V
Switching voltage DC max.	125 V
Switching current max.	1 A
Switching current DC	1 mA
Switching frequency max.	15 Hz
Power rating AC max.	60 VA
Power rating DC max.	30 W
Switching capacity AC-12 (EN IEC 60947-5-1)	0.5 A (50 V AC)
Utilization category AC-15 (EN IEC 60947-5-1)	0.25 A @ 50 V

Diagnostics

Status indication LED	yellow
-----------------------	--------

Device protection

Condition lifetime	load-dependent
--------------------	----------------

Device protection | Electrical

Electrical lifetime	100,000,000 Cycles
Rated surge voltage	1.5 kV

Device protection | Mechanical

Mechanical endurance	100,000,000 Cycles
----------------------	--------------------

Mechanical data

Response time max.	10 ms
Drop-out time max.	10 ms
Bounce time max.	1 ms

Mechanical data | Material data

Material contact	Pd Ni-Au Rh
------------------	-------------

Mechanical data | Mounting data

Height	56 mm
Width	12 mm
Depth	64 mm
Mounting method	geschnappt
Suitable for mounting type	Mounting rail TH35, (EN 60715), G32

Environmental characteristics | Climatic

Operating temperature min.	-20 °C
Operating temperature max.	60 °C

Connection type 2

Connection type 1	X1
Connection type 2	X2
Family construction form	terminal
No. of poles	2
Gender	female
Color contact carrier	green
Connection	Screw terminals SK
PIN 1	A 1
PIN 2	A 2
Family construction form	terminal
No. of poles	2
Gender	female
Color contact carrier	green
Connection	Screw terminals SK
PIN 1	13
PIN 2	14