

RMME 11/24 WITH GROUND BRIDGE INPUT RELAY

to be discontinued - Last Time Order: 2024-10-31

Art.No.: 51860

Weight: 0.028

Country of origin: CZ

Model designation: RMME 11/24 M.SCH.MASSE



1 relay; 1 NO contact

1 A

24 V AC/DC

with minus plug link

Screw terminals

[Link to Product](#)**Illustration**

Product may differ from Image

**Header**

Material short text

RMME 11/24 M.SCH.MASSE

Commercial data

The information in this Product-PDF has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2025-09-22

Murrelektronik GmbH | Grabenstraße 29 | 71570 Oppenweiler | Fon +49 (71 91) 47-0 | Fax +49 (71 91) 47-491000 | shop@murrelektronik.com | shop.murrelektronik.com

URL Webshop	https://shop.murrelektronik.com/51860
GTIN	4048879027328
Scope of delivery	Jumper (Art-No. 90960)
ECLASS-6.0	27371001
ECLASS-6.1	27371601
ECLASS-7.0	27371601
ECLASS-7.1	27371601
ECLASS-8.0	27371601
ECLASS-8.1	27371601
ECLASS-9.0	27371601
ECLASS-9.1	27371601
ECLASS-10.0.1	27371601
ECLASS-10.1	27371601
ECLASS-11.0	27371601
ECLASS-11.1	27371601
ECLASS-12.0	27371601
ECLASS-13.0	27371601
ECLASS-14.0	27371601
ETIM-5.0	EC001437
ETIM-6.0	EC001437
ETIM-7.0	EC001437
ETIM-8.0	EC001437
customs tariff number	85364900
EAN	4048879027328
Packaging unit	1

Electrical data | Input

Input voltage AC	24 V
Input voltage AC min.	216 V
Input voltage AC max.	264 V
Input voltage DC	24 V
Input voltage DC min.	21.6 V
Input voltage DC max.	264 V
Input current	6 mA

Electrical data | Output

Switching voltage AC max.	125 V
Switching voltage DC max.	125 V
Switching current max.	1 A
Switching current DC	1 mA
Switching frequency max.	15 Hz
Power rating AC max.	60 VA
Power rating DC max.	30 W
Switching capacity AC-15 (EN IEC 60947-5-1)	1 A (24 V AC); 0.5 A (125 V AC)
Utilization category DC-13 (EN IEC 60947-5-1)	1 A @ 24 V 0.5 A @ 125 V

Diagnostics

Status indication LED	yellow
-----------------------	--------

Device protection

Condition lifetime	load-dependent
--------------------	----------------

Device protection | Electrical

Electrical lifetime	0 cycles
Rated surge voltage	1.5 kV

Device protection | Mechanical

Mechanical endurance	0 cycles
----------------------	----------

Mechanical data	
Response time max.	10 ms
Drop-out time max.	10 ms
Bounce time max.	1 ms
Mechanical data Material data	
Material contact	Pd Ni-Au Rh
Mechanical data Mounting data	
Height	56 mm
Width	12 mm
Depth	65 mm
Mounting method	geschnappt
Suitable for mounting type	Mounting rail TH35, (EN 60715), G32
Environmental characteristics Climatic	
Operating temperature min.	-25 °C
Operating temperature max.	60 °C
Connection type 2	
Family construction form	terminal
No. of poles	2
Gender	female
Connection	Screw terminals SK
PIN 1	13
PIN 2	14
Family construction form	terminal
No. of poles	2
Gender	female
Connection	Screw terminals SK
PIN 1	A 1
PIN 2	A 2