

MVK MPNIO DI8 DO8 M12L 4P galvanic separation

MVK ProfiNet, metal

Art.No.: 55164

Weight: 0.925

Country of origin: DE

Model designation: MVK MPNIO DI8 DO8 M12L 4P

Digital inputs/outputs

DI8 DO8 (IRT)

Ethernet 10/100 Mbit/s; M12, D-coded

M12 power, 4-pin, L-coded, 2× max. 12 A

M12, 5-pole, A-coded

FSU (Fast-Start-Up)


Galvanic isolation

Connection cables are in the online shop under "Connection Technology".

Housing fully potted.

Link to Product**Illustration**

Product may differ from Image

**Commercial data**

URL Webshop	https://shop.murrelektronik.com/55164
GTIN	4048879852227
ECLASS-6.1	27242604
ECLASS-7.0	27242604
ECLASS-7.1	27242604
ECLASS-8.0	27242604
ECLASS-8.1	27242604
ECLASS-9.0	27242604
ECLASS-9.1	27242604
ECLASS-10.0.1	27242604
ECLASS-10.1	27242604
ECLASS-11.0	27242604
ECLASS-11.1	27242604

ECLASS-12.0	27242604
ECLASS-13.0	27242604
ECLASS-14.0	27242604
EAN	4048879852227

Electrical data | Supply

Norm operating voltage	EN 61131-2
Operating voltage US DC	24 V
Total current US max.	12 A
Operating voltage UA DC	24 V
Total current UA max.	12 A

Electrical data | Input

Sensor current US per input max.	0.2 A
Short-circuit protected	yes
Overload resistant	yes
Type input	for 3-wire sensors or mechanical switches, PNP

Electrical data | Output

Output current per pin max.	2 A
Overload resistant	yes
Short-circuit protected	yes

Industrial communication

Supported protocol	PROFINET
--------------------	----------

Industrial communication | Profinet

PROFINET conformance class	C
PROFINET addressing	DCP
PROFINET Netload Class	III
PROFINET specification	V2.3
IRT (network communication)	yes
MRP client	yes
FSU (Fast-Start-Up)	yes
Fast start up time max.	0.5 s
Shared device/input	yes
Number of active connections (IO controller) max.	2

Diagnostics

Actuator warning	per channel via LED and BUS
Short circuit diagnosis	yes
Overload diagnosis	yes
Cable break	per port
Diagnostic	No voltage, Under voltage
Diagnostic via BUS	per module and channel
Diagnostic via LED	per module and channel
LED display	Ethernet connection/data traffic

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP67
-------------------------------------	------

Mechanical data | Mounting data

Height	42 mm
Width	63 mm
Depth	225 mm
Suitable for mounting type	2-hole screw mounting

Environmental characteristics | Climatic

Operating temperature min.	-25 °C
----------------------------	--------

Operating temperature max.	55 °C
Storage temperature min.	-25 °C
Storage temperature max.	70 °C
Connection type 5	
Connection type 1	X0-X3
Connection type 2	X4-X7
Connection type 3	XD1
Connection type 4	XD2
Connection type 5	XF2
Family construction form	M12
No. of poles	5
Coding	A
Gender	female
Color contact carrier	black
PIN 1	n.c.
PIN 2	DO (UA)
PIN 3	0 V (UA)
PIN 4	DO (UA)
PIN 5	PE
Family construction form	M12
No. of poles	5
Coding	A
Gender	female
Color contact carrier	black
PIN 1	24 V DC (US)
PIN 2	DI
PIN 3	0 V (US)
PIN 4	DI
PIN 5	PE
Family construction form	M12
No. of poles	5
Coding	L
Gender	male
Color contact carrier	black
PIN 1	24 V DC (US)
PIN 2	0 V
PIN 3	0 V
PIN 4	24 V DC (UA)
PIN 5	n.c.
Family construction form	M12
No. of poles	4
Coding	L
Gender	female
Color contact carrier	black
PIN 1	24 V DC (UB 1) (US)
PIN 2	0 V (UA)
PIN 3	0 V (UB 1) (US)
PIN 4	24 V DC (UA)
Family construction form	M12
No. of poles	4
Coding	D
Gender	female
Color contact carrier	black

Mounting method	inserted, screwed
Tightening torque	0.6 Nm
PIN 1	TD +
PIN 2	RD +
PIN 3	TD -
PIN 4	RD -