

POTENTIAL TERMINAL BLOCK BLUE YELLOW

Art.No.: 56110
Weight: 0.079
Country of origin: CZ
Model designation: Potenzialklemmenblock blau gelb


Potential terminal block
blue/yellow

Link to Product

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27141106
ECLASS-6.1	27141106
ECLASS-7.0	27141106
ECLASS-8.0	27141106
ECLASS-9.0	27141106
ECLASS-10.1	27141106
ECLASS-11.1	27141106
ECLASS-12.0	27141106
ETIM-5.0	EC001283
ETIM-6.0	EC001283
ETIM-7.0	EC001283
ETIM-8.0	EC001283
customs tariff number	85369010
customs tariff number	85369010
GTIN	4048879049368
GTIN	4048879049368
Packaging unit	1
Packaging unit	1
Electrical data Supply	
Operating voltage AC max.	30 V
Operating voltage DC max.	30 V

Total current max.	10 A
--------------------	------

Installation

Connection cross section max.	2,5 mm ²
-------------------------------	---------------------

AWG number min.	28
-----------------	----

AWG number max.	14
-----------------	----

Installation | Connection

Connection	Spring clamp plug-in terminals
------------	--------------------------------

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP20
-------------------------------------	------

Mechanical data | Mounting data

Height	70 mm
--------	-------

Width	56 mm
-------	-------

Depth	32,5 mm
-------	---------

Environmental characteristics | Climatic

Operating temperature min.	0 °C
----------------------------	------

Operating temperature max.	55 °C
----------------------------	-------

Storage temperature min.	-40 °C
--------------------------	--------

Storage temperature max.	85 °C
--------------------------	-------