

CUBE67 Hygienic Design I/O EXTENSION MODULE

8 multifunction channels

Art.No.: 5661160

Weight: 0.242

Country of origin: DE

Model designation: Cube67 DIO8 E 4xM12 HD

Expansion module

DIO8 - 0.5 A (E) - 4x M12

short-circuit and overload protected

Digital inputs/outputs (multifunctional)

Hygienic Design

Stainless steel, polished

Connection cables are in the online shop under "Connection Technology".

Housing fully potted.


Connection cable: F&B, F&B Pro, Steel

[Link to Product](#)

Illustration



Product may differ from Image



Header

Material short text Cube67 DIO8 E 4xM12 HD

Commercial data

URL Webshop	https://shop.murrelektronik.com/5661160
GTIN	4048879697309
ECLASS-6.0	27242604
ECLASS-6.1	27242604
ECLASS-7.0	27242604
ECLASS-7.1	27242604
ECLASS-8.0	27242604
ECLASS-8.1	27242604
ECLASS-9.0	27242604
ECLASS-9.1	27242604

ECLASS-10.0.1	27242604
ECLASS-10.1	27242604
ECLASS-11.0	27242604
ECLASS-11.1	27242604
ECLASS-12.0	27242604
ECLASS-13.0	27242604
ECLASS-14.0	27242604
ETIM-5.0	EC001855
ETIM-6.0	EC001855
ETIM-7.0	EC001855
ETIM-8.0	EC001855
customs tariff number	85389099
EAN	4048879697309
Packaging unit	1

Electrical data | Supply

Norm operating voltage	IEC/EN 61131-2
Operating voltage US DC	24 V
Total current US max.	4 A
Operating voltage UA DC	24 V
Total current UA max.	4 A
Current consumption max.	50 mA

Electrical data | Input

Sensor current US per input max.	0.2 A
Short-circuit protected	yes
Overload resistant	yes
Input filter time	1 ms
Type input	for 3-wire sensors or mechanical switches, PNP

Electrical data | Output

Output current per pin max.	0.5 A
Overload resistant	yes
Short-circuit protected	yes
Lamp load	10 W

Diagnostics

Actuator warning	per channel via LED and BUS
Short circuit diagnosis	yes
Overload diagnosis	yes
Diagnostic	No voltage, Under voltage
Diagnostic via BUS	per module and channel
Diagnostic via LED	per module and channel
LED display	Ethernet connection/data traffic

Device protection | Electrical

Degree of protection (ISO 20653:2013)	IP69K
---------------------------------------	-------

Mechanical data | Mounting data

Height	54 mm
Width	32 mm
Depth	177 mm
Suitable for mounting type	2-hole screw mounting

Environmental characteristics | Climatic

Operating temperature min.	0 °C
Operating temperature max.	55 °C
Storage temperature min.	-20 °C

Storage temperature max. 75 °C

Connection type 3	
Connection type 1	0-3
Connection type 2	Bus In
Connection type 3	Bus Out
Family construction form	M12
No. of poles	5
Coding	A
Gender	male
Color contact carrier	black
PIN 1	24 V DC (US)
PIN 2	DI / DO 0.x
PIN 3	0 V
PIN 4	DI / DO 1.x
PIN 5	PE
Family construction form	M12
No. of poles	6
Coding	A
Gender	male
Color contact carrier	black
PIN 1	24 V DC (UA)
PIN 2	24 V DC (US)
PIN 3	0 V
PIN 4	Bus internal
PIN 5	Bus internal
PIN 6	0 V
Family construction form	M12
No. of poles	6
Coding	A
Gender	female
Color contact carrier	black
PIN 1	24 V DC (UA)
PIN 2	24 V DC (US)
PIN 3	0 V
PIN 4	Bus internal
PIN 5	Bus internal
PIN 6	0 V