

Bus terminating plug M12 male B-cod.

Profibus

Art.No.: 7000-14041-0000000

Weight: 0.01

Country of origin: DE

Model designation: MSBA05L0-T 1-4R.2-3R.2-4R



PROFIBUS

Terminating resistor


Male

M12, 4-pole

B-coded

[Link to Product](#)**Illustration**

Product may differ from Image

**Side 1**

Tightening torque 0,6 Nm

Family construction form M12

The information in this Product-PDF has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2025-05-04

Murrelektronik GmbH | Grabenstraße 29 | 71570 Oppenweiler | Fon +49 (71 91) 47-0 | Fax +49 (71 91) 47-491000 | shop@murrelektronik.com | shop.murrelektronik.com

Thread	M12 x 1
Degree of protection (EN IEC 60529)	IP67
Commercial data	
ECLASS-6.0	19070403
ECLASS-6.1	19070403
ECLASS-7.0	19070403
ECLASS-8.0	19070403
ECLASS-9.0	19070403
ECLASS-10.1	19070403
ECLASS-11.1	19070403
ECLASS-12.0	19070403
ETIM-5.0	EC001855
customs tariff number	85331000
customs tariff number	85331000
GTIN	4048879198592
GTIN	4048879198592
Packaging unit	1
Packaging unit	1
Electrical data Supply	
Operating voltage DC max.	30 V
Operating voltage DC max. (UL-listed)	30 V
Current operating per contact max.	4 A
Installation Pin assignment	
Coding	B
Device protection Electrical	
Additional condition protection degree	inserted, screwed
Pollution Degree	3
Rated surge voltage	0,8 kV
Material group (IEC 60664-1)	I
Mechanical data Material data	
Coating locking	Nickel
Locking material	Zinc die-casting
Mechanical data Mounting data	
Mounting method	inserted, screwed, Shaking protection
Environmental characteristics Climatic	
Operating temperature min.	-25 °C
Operating temperature max.	85 °C