MURR ELEKTRONIK
stay connected

M12 male recept. A-cod. front

TPE-wires 12x0.14 0.5m

Art.No.: 7000-19161-9790050
Weight: 0.05
Country of origin: DE
Model designation: MSAFV-12E979_0.5

Flange male
M12, 12-pole
Front mounting
with multi-strand wire

Link to Product

Illustration







The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2025-10-05

MURR ELEKTRONIK
stay connected





Product may differ from Image

Header	
Cable length	0,50 m
Side 1	
Family construction form	M12
No. of poles	12
Coding	A
Mounting method	inserted, screwed
Thread	M12 x 1
Tightening torque	0.6 Nm
Width across flats	SW14
Material	Zinc die-casting
Material contact	Copper alloy
Coating contact	gold plated
Degree of protection (EN IEC 60529)	IP67
Commercial data	
URL Webshop	https://shop.murrelektronik.com/7000-19161-9790050
customs tariff number	85444290
EAN	4048879294812
Packaging unit	1
Electrical data | Supply	
Operating voltage AC max.	30 V
Operating voltage DC max.	30 V
Current operating per contact max.	1.5 A
Diagnostics	
Status indication LED	no
Installation | Connection	
Mounting set	M16 x 1.5
Device protection | Electrical	
Degree of protection (EN IEC 60529)	IP67
Protection NEMA	6P, 4, 3
Additional condition protection degree	inserted, screwed
Pollution Degree	3

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2025-10-05

Rated surge voltage	0.8 kV
Material group (IEC 60664-1)	I
Mechanical data	
Contour for corrugated hose	without
Mechanical data | Material data	
Coating housing	nickel plated
Material screw connection	Zinc die-casting
Coating of fitting	nickel plated
Mechanical data | Mounting data	
Mounting method	inserted, screwed
Environmental characteristics | Climatic	
Operating temperature min.	-30 °C
Operating temperature max.	85 °C
Additional condition temperature range	depending on cable quality
Important installation notes	
Note on bending radius	**Attention:** Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.
Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.
Conformity	
Product standard	DIN EN 61076-2-101 (M12)
Approvals	
UL 50E	yes
Installation | Cable	
Cable identification	979
Wire arrangement	brown, blue, white, green, pink, yellow, black, gray, red, violet, gray-pink, red-blue
Material wire insulation	PP
Amount wires	12
Outer diameter insulation	1.25 mm
Conductor crosssection (wire)	0.14 mm²
Min. operating temperature (static)	-40 °C
Max. operating temperature (fixed)	85 °C
Operating temperature min. (dynamic)	-25 °C
Operating temperature max. (dynamic)	85 °C
Bending radius (fixed)	5 × Outer diameter
Bending radius (dynamic)	15 × Outer diameter

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2025-10-05