

SVS Eco valve plug CI-9.4mm screw terminal

2-pol. + FE, max. 0,5mm², 4 -6mm, LED+VDR 24V

Art.No.: 7000-30205-0000000

Weight: 0.02

Country of origin: HU

Model designation: MSVSE-RB1X-M12 SVS Eco LED

Form CI (9.4 mm)

24 V AC/DC $\pm 15\%$




LED and VDR


metric

Field wireable (screw terminals)

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)**Illustration**



Product may differ from Image

**Side 1**

Mounting method	inserted, screwed
Degree of protection (EN IEC 60529)	IP65

Commercial data

URL Webshop	https://shop.murrelektronik.com/7000-30205-0000000
customs tariff number	85366990
EAN	4048879186964
Packaging unit	1

Electrical data | Supply

Operating voltage AC	24 V
Operating voltage AC min.	20.4 V
Operating voltage AC max.	26.4 V
Operating voltage DC	24 V
Operating voltage DC min.	20.4 V
Operating voltage DC max.	26.4 V
Current operating per contact max.	1.5 A

Diagnostics

Status indication LED	yellow
-----------------------	--------

Installation

Connection cross section min.	0.34 mm ²
Connection cross section max.	0.5 mm ²

Installation | Connection

Tightening torque	0.4 Nm
Tightening torque tolerance	± 0.1 Nm
Tightening torque clamping screw	0.2 Nm
Mounting set	M12 x 1.5

Installation | Pin assignment

No. of poles	PE
--------------	----

Device protection | Electrical

Additional condition protection degree	inserted, screwed
Additional suppressor	Varistor

Mechanical data Material data	
Material housing	PA
Color housing	opaque
Material gasket	NBR
Mechanical data Mounting data	
fastening screw	M3x31
Clamping range min.	4 mm
Clamping range max.	6 mm
Environmental characteristics Climatic	
Operating temperature min.	-40 °C
Operating temperature max.	90 °C
Important installation notes	
Note on bending radius	Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.
Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.