

M8 panel feed through male / female 0° A-cod.

4-pol., shielded

Art.No.: 7000-88112-0000000

Weight: 0.035

Country of origin: DE

Model designation: MSFL0-H-T Schaltschrankdurchführung




Control cabinet entry system


Male - female

M8, 4-pole

Rear mounting

shielded

[Link to Product](#)**Illustration**



Product may differ from Image

Side 1

Family construction form	M8
Material contact	Copper alloy
No. of poles	4

Commercial data

ECLASS-6.0	27143423
ECLASS-7.0	27449001
ECLASS-8.0	27449001
ECLASS-9.0	27440321
ECLASS-10.1	27440109
ECLASS-11.1	27440109
ECLASS-12.0	27440109
ETIM-5.0	EC002640
customs tariff number	85366990
customs tariff number	85366990
EAN	4048879689304
EAN	4048879689304
Packaging unit	1
Packaging unit	1

Electrical data | Supply

Operating voltage DC	60 V
Current operating per contact max.	4 A

Diagnostics

Status indication LED	no
-----------------------	----

Installation | Connection

Mating cycles min.	100
--------------------	-----

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP67
Additional condition protection degree	inserted, screwed
Pollution Degree	3
Rated surge voltage	1,5 kV
Overvoltage category (EN 60950-1)	II

Mechanical data

Contour for corrugated hose	without
-----------------------------	---------

Mechanical data | Material data

Material housing	Metal
------------------	-------

Coating contact	gold plated
-----------------	-------------

Material contact carrier	PA
--------------------------	----

Mechanical data | Mounting data

Mounting method	inserted, screwed
-----------------	-------------------

Environmental characteristics | Climatic

Operating temperature min.	-25 °C
----------------------------	--------

Operating temperature max.	85 °C
----------------------------	-------

Important installation notes

Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.
-----------------------	---

Note on bending radius	Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.
------------------------	---