

M12 male 0° A-cod. IDC




3-pol., 0.5 - 1.0mm², 5,5 - 8mm

Art.No.: 7000-12511-0000000
Weight: 0.02
Country of origin: DE
Model designation: MSAL0-AF-W-IDC

Male straight
M12, 3-pole
IDC terminals
Connection cross section: 0.5...1.0 mm²
Art.-No. 7005 - M12 Lite - (plastic hexagonal screw) on request
Plastic housings with good resistance against chemicals and oils.
The resistance to aggressive media should be individually tested for your application. Further details on request.

Link to Product

Illustration



Product may differ from Image

Header

Material short text MSAL0-AF-W-IDC

Side 1

Family construction form M12
Degree of protection (EN IEC 60529) IP67

Commercial data	
URL Webshop	https://shop.murrelektronik.com/7000-12511-0000000
GTIN	4048879201810
ECLASS-6.0	27279221
ECLASS-6.1	27260702
ECLASS-7.0	27440102
ECLASS-7.1	27440102
ECLASS-8.0	27440102
ECLASS-8.1	27440102
ECLASS-9.0	27440116
ECLASS-9.1	27440106
ECLASS-10.0.1	27440106
ECLASS-10.1	27440102
ECLASS-11.0	27440106
ECLASS-11.1	27440102
ECLASS-12.0	27440116
ECLASS-13.0	27440106
ECLASS-14.0	27440106
ETIM-5.0	EC002635
ETIM-6.0	EC002635
ETIM-7.0	EC002635
ETIM-8.0	EC002635
customs tariff number	85366990
EAN	4048879201810
Packaging unit	1
Electrical data Supply	
Operating voltage AC max.	32 V
Operating voltage DC max.	32 V
Current operating per contact max.	4 A
Installation	
Single wire diameter min.	0.1 mm
Connection cross section min.	0.5 mm ²
Connection cross section max.	1 mm ²
Installation Connection	
Tightening torque	0.6 Nm
Wire insulation diameter min.	1.6 mm
Wire insulation diameter max.	2 mm
Device protection Electrical	
Additional condition protection degree	inserted, screwed
Mechanical data Mounting data	
Height	57.3 mm
Width	22 mm
Depth	22 mm
Mounting method	inserted, screwed, Shaking protection
Clamping range min.	5.5 mm
Clamping range max.	8 mm
Environmental characteristics Climatic	
Operating temperature min.	-25 °C
Operating temperature max.	85 °C
Important installation notes	
Note on bending radius	Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.

Note on strain relief

Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.