

**M12 male 0° A-cod. IDC**

4-pol., 0,14 - 0,34mm<sup>2</sup>, 4,5 - 8,8mm, shielded

Art.No.: 7000-12551-0000000

Weight: 0.052

Country of origin: RO

Model designation: MSAL0-AC-T MOSA 0,14-0,34qmm

Male straight



M12, 4-pole

IDC terminals

Connection cross section: 0.14...0.34 mm<sup>2</sup>

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

**[Link to Product](#)****Illustration**

Product may differ from Image

**Header**

Material short text

MSAL0-AC-T MOSA 0,14-0,34qmm

**Side 1**

Family construction form	M12
Degree of protection (EN IEC 60529)	IP67

**Commercial data**

URL Webshop	<a href="https://shop.murrelektronik.com/7000-12551-0000000">https://shop.murrelektronik.com/7000-12551-0000000</a>
GTIN	4048879306027
ECLASS-6.0	27279221
ECLASS-6.1	27260702
ECLASS-7.0	27440102
ECLASS-7.1	27440102
ECLASS-8.0	27440102
ECLASS-8.1	27440102
ECLASS-9.0	27440116
ECLASS-9.1	27440106
ECLASS-10.0.1	27440106
ECLASS-10.1	27440102
ECLASS-11.0	27440106
ECLASS-11.1	27440102
ECLASS-12.0	27440116
ECLASS-13.0	27440106
ECLASS-14.0	27440106
ETIM-5.0	EC002635
ETIM-6.0	EC002635
ETIM-7.0	EC002635
ETIM-8.0	EC002635
customs tariff number	85366990
EAN	4048879306027
Packaging unit	1

**Electrical data | Supply**

Operating voltage AC max.	50 V
Operating voltage DC max.	50 V
Current operating per contact max.	4 A

**Installation**

Single wire diameter min.	0.1 mm
Connection cross section min.	0.14 mm²
Connection cross section max.	0.34 mm²

**Installation | Connection**

Wire insulation diameter min.	12 mm
Wire insulation diameter max.	16 mm

**Device protection | Electrical**

Additional condition protection degree	inserted, screwed
--	-------------------

**Mechanical data | Mounting data**

Height	52 mm
Width	19.5 mm
Depth	19.5 mm
Clamping range min.	5.5 mm
Clamping range max.	7.2 mm

**Environmental characteristics | Climatic**

Operating temperature min.	-25 °C
Operating temperature max.	85 °C

**Important installation notes**

Note on bending radius	<b>Attention:</b> Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.
Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.