


Cable drum Ø 500mm

PUR 4x0.75 gy UL/CSA 500m  
Art.No.: 7000-C0505-8620000  
Weight: 31.5  
Country of origin: PL  
Model designation: 500m Kabel 10080943(862)auf Kabeltrommel


Cable drum (500 m)  
4× 0.75 mm², gray  
PUR (UL/CSA)  
suitable for C-tracks

Link to Product

Illustration



Product may differ from Image



| Commercial data       |                 |
|-----------------------|-----------------|
| ECLASS-6.0            | 27062011        |
| ECLASS-6.1            | 27061801        |
| ECLASS-7.0            | 27061801        |
| ECLASS-8.0            | 27061801        |
| ECLASS-9.0            | 27061801        |
| ECLASS-10.1           | 27061801        |
| ECLASS-11.1           | 27061801        |
| ECLASS-12.0           | 27061801        |
| ETIM-5.0              | EC001855        |
| customs tariff number | 85444995        |
| customs tariff number | 85444995        |
| EAN                   | 4048879690034   |
| EAN                   | 4048879690034   |
| Packaging unit        | 1               |
| Packaging unit        | 1               |
| Installation   Cable  |                 |
| Cable identification  | 862             |
| Cable Type            | 3               |
| Jacket Color          | gray            |
| Type of Certificate   | cURus           |
| Amount stranding      | 1               |
| Stranding             | 4 wires twisted |

|                                                   |                                                                |
|---------------------------------------------------|----------------------------------------------------------------|
| wire arrangement                                  | brown, black, blue, white                                      |
| Cable weight                                      | 67,1 g/m                                                       |
| Material jacket                                   | PUR                                                            |
| Shore hardness jacket                             | 90 ± 5 Shore A                                                 |
| Freedom from ingredients (jacket)                 | lead-free, cadmium-free, CFC-free, halogen-free, silicone-free |
| Outer-diameter (jacket)                           | 6,5 mm                                                         |
| Tolerance outer diameter (sheath)                 | ± 5 %                                                          |
| Material wire insulation                          | PP                                                             |
| Amount wires                                      | 4                                                              |
| Outer diameter insulation                         | 1,85 mm                                                        |
| Outer diameter tolerance core insulation          | ± 5 %                                                          |
| Shore hardness wire insulation                    | 70 ± 5 Shore D                                                 |
| Ingredient freeness wire insulation               | lead-free, cadmium-free, CFC-free, halogen-free, silicone-free |
| Amount strands (wire)                             | 42                                                             |
| Diameter of single wires                          | 0,15 mm                                                        |
| Conductor crosssection (wire)                     | 0,75 mm <sup>2</sup>                                           |
| Material conductor wire                           | Stranded copper wire, bare                                     |
| Conductor type (wire)                             | strand class 6                                                 |
| Nominal voltage AC max.                           | 300 V                                                          |
| Current load capacity (standard)                  | to DIN VDE 0298-4                                              |
| Current load capacity min. wire                   | 9,6 A                                                          |
| Electrical resistance line constant wire          | 26 Ω/km @ 20 °C                                                |
| AC withstand voltage (wire - wire)                | 2,5 kV @ 60 s                                                  |
| Power frequency withstand voltage (wire - jacket) | 2,5 kV @ 60 s                                                  |
| Min. operating temperature (static)               | -40 °C                                                         |
| Max. operating temperature (fixed)                | 80 °C / 90 °C @ 10000 h Operation                              |
| Operating temperature min. (dynamic)              | -25 °C                                                         |
| Operating temperature max. (dynamic)              | 80 °C / 90 °C @ 10000 h Operation                              |
| Flame resistance                                  | UL 1581 § 1100 FT2   IEC 60332-2-2   UL 1581 § 1090            |
| chemical resistance                               | Good, application-related testing                              |
| Gasoline resistance                               | Good, application-related testing                              |
| Oil resistance                                    | Good, application-related testing   DIN EN 60811-404           |
| Bending radius (fixed)                            | 5 x Outer diameter                                             |
| Bending radius (dynamic)                          | 10 x Outer diameter                                            |
| No. of bending cycles (C-track)                   | 10 Mio. @ 25 °C                                                |
| Traversing distance (C-track)                     | 10 m @ 25 °C   horizontal                                      |
| Travel speed (C-track)                            | 3 m/s @ 25 °C                                                  |
| No. of torsion cycles                             | 2 Mio.                                                         |
| Torsion stress                                    | ± 180 °/m                                                      |
| Torsion speed                                     | 35 cycles/min                                                  |