

SVS Eco valve plug CI-9.4mm screw terminal3-pol. + PE, max. 0,5mm², 5 -6mm

Art.No.: 7000-30245-0000000

Weight: 0.012

Country of origin: HU

Model designation: MSVSE-RB5K-M12 SVS Eco

Form CI (9.4 mm)

max. 250 V AC/DC




without components



metric

field-wireable

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)**Illustration**



Product may differ from Image

**Side 1**

Mounting method	inserted, screwed
Degree of protection (EN IEC 60529)	IP65

Commercial data

URL Webshop	https://shop.murrelektronik.com/7000-30245-0000000
customs tariff number	85366990
EAN	4048879513715
Packaging unit	1

Electrical data | Supply

Operating voltage AC max.	250 V
Operating voltage DC max.	250 V
Current operating per contact max.	6 A

Installation

Connection cross section max.	0.5 mm ²
-------------------------------	---------------------

Installation | Connection

Tightening torque	0.4 Nm
Tightening torque tolerance	± 0.1 Nm
Tightening torque clamping screw	0.2 Nm
Mounting set	M12 x 1.5

Installation | Pin assignment

No. of poles	PE
--------------	----

Device protection | Electrical

Additional condition protection degree	locked, inserted
--	------------------

Mechanical data | Material data

Material gasket	NBR
-----------------	-----

Mechanical data | Mounting data

Fastening screw	M3x31
Clamping range min.	5 mm
Clamping range max.	6 mm

Environmental characteristics | Climatic

Operating temperature min.	-40 °C
----------------------------	--------

Operating temperature max. 90 °C

Important installation notes

Note on bending radius **Attention:** Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.

Note on strain relief Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.