

M23 servo cable

specification: 6FX5002-5CA15-1BA0

Art.No.: 7000-PS105-8691000

Weight: 1.863

Country of origin: DE

Model designation: M6FX5002-5CA15-1BA0

Power cable for SINAMICS S120 and Motors with M23 connection

Female straight – male straight

M23 – M23, 6-pole

4-pole used

shielded

without brake wires

without cable sleeves

Further cable lengths on request.




Plastic housings with good resistance against chemicals and oils.



Power cores: 12 A (1.5 mm²), 15 A (2.5 mm²)

The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)

Illustration





Product may differ from Image



Header	
Material short text	M6FX5002-5CA15-1BA0
Cable length	10,00 m
Side 1	
Family construction form	M23
Thread	M23 x 1
Tightening torque	2 Nm
Width across flats	SW27
suitable for corrugated tube (internal Ø)	16 mm
Side 2	
Family construction form	M23
suitable for corrugated tube (internal Ø)	23 mm
Commercial data	
URL Webshop	https://shop.murrelektronik.com/7000-PS105-8691000
GTIN	4048879507448
ECLASS-6.0	27279218
ECLASS-6.1	27279218
ECLASS-7.0	27279218

ECLASS-7.1	27279218
ECLASS-8.0	27279218
ECLASS-8.1	27279218
ECLASS-9.0	27060327
ECLASS-9.1	27060311
ECLASS-10.0.1	27060311
ECLASS-10.1	27060311
ECLASS-11.0	27060311
ECLASS-11.1	27060311
ECLASS-12.0	27060327
ECLASS-13.0	27060311
ECLASS-14.0	27060311
ETIM-5.0	EC001855
ETIM-6.0	EC001855
ETIM-7.0	EC001855
ETIM-8.0	EC001855
customs tariff number	85444290
EAN	4048879507448
Packaging unit	1

Electrical data | Supply

Operating voltage AC max.	630 V
Operating voltage DC max.	630 V

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP67, IP65
Additional condition protection degree	inserted, screwed
Pollution Degree	3
Rated surge voltage	6 kV
Material group (IEC 60664-1)	I

Mechanical data | Material data

Material housing	PUR
Locking material	Brass
Coating locking	nickel plated

Mechanical data | Mounting data

Mounting method	inserted, screwed, Shaking protection
-----------------	---------------------------------------

Environmental characteristics | Climatic

Operating temperature min.	-25 °C
Operating temperature max.	85 °C
Additional condition temperature range	depending on cable quality

Important installation notes

Note on bending radius	Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.
Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.

Installation | Cable

Cable identification	869
Amount stranding	1
Stranding	Wires
Cable shielding (type)	copper braid, tinned
Cable shielding (coverage)	85 %
Pair shielding (type)	copper braid, tinned
Pair shielding (coverage)	85 %
Banding	Fiber tape, Fleece
Filler	yes

Cable weight	167 g/m
Material wire insulation (type 3)	TPM
Outer diameter wire insulation (type 3)	3 mm
Tolerance outer diameter wire insulation (type 3)	± 0,1 mm
Ingredient freeness wire insulation (type 3)	CFC-free, silicone-free, lead-free
Printing colour wire insulation (type 3)	white (isolation black)
Amount wires (type 3)	4
Amount strands wire (type 3)	50
Diameter of single wires (type 3)	0,25 mm
Wire conductor cross section (type 3)	2,5 mm ²
Material conductor wire (type 3)	Stranded copper wire, bare
Conductor type wire (type 3)	Strand class 5
Outer-diameter (jacket)	9,7 mm
Tolerance outer diameter (sheath)	± 5 %
Material jacket	PVC
Freedom from ingredients (jacket)	CFC-free, silicone-free, lead-free
Conductor resistance (wire type 3)	7.98 Ω/km @ 20 °C
Electrical capacity line constant (wire - wire) (power)	150.000 pF/km
Electrical capacity line constant (wire - shield) (power)	250.000 pF/km
Isolation resistance	10 MΩ × km
Max. rated voltage (conductor - ground)	600 V
Max. rated voltage (conductor - conductor)	1.000 V
Withstand voltage (wire - wire)	4 kV @ 60 s
Withstand voltage (wire - jacket)	4 kV @ 60 s
Withstand voltage (wire - shield)	4 kV @ 60 s
Current load capacity (standard)	to DIN VDE 0298-4
Current carrying capacity min. wire (type 3)	20,8 A
Min. operating temperature (static)	-25 °C
Max. operating temperature (static)	80 °C
Operating temperature min. (dynamic)	-5 °C
Operating temperature max. (dynamic)	60 °C
Operating temperature min. (drag chain)	-5 °C
Operating temperature max. (drag chain)	60 °C
Bending radius (fixed)	5 × Outer diameter
Bending radius (dynamic)	18 × Outer diameter
No. of bending cycles (C-track)	0.1 Mio. @ 25 °C
Traversing distance (C-track)	5 m @ 25 °C horizontal
Travel speed (C-track)	0.5 m/s @ 25 °C
Acceleration (C-track)	2 m/s ² @ 25 °C
Torsion stress	30 °C