

**RJ45 male 45° left / RJ45 male 45° right shielded**

PUR 1x4xAWG22 shielded gn UL/CSA+drag ch. 1m

Art.No.: 7000-74561-7960100

Weight: 0.087

Country of origin: DE

Model designation: MSRFL0-RG-8p4c796\_1.0

Product fulfills requirements according to UN/ECE R118

Ethernet CAT5

Male 45° left – male 45° right




RJ45 – RJ45, 4-pole


shielded

Further cable lengths on request.



Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

**[Link to Product](#)****Illustration**



Product may differ from Image



|                                     |               |
|-------------------------------------|---------------|
| Cable length                        | 1 m           |
| Side 1                              |               |
| Mounting method                     | pluggable     |
| Family construction form            | RJ45          |
| Gender                              | male          |
| Cable outlet                        | angled        |
| Material                            | PUR           |
| No. of poles                        | 4             |
| Degree of protection (EN IEC 60529) | IP20          |
| Side 2                              |               |
| Mounting method                     | pluggable     |
| Family construction form            | RJ45          |
| Gender                              | male          |
| Cable outlet                        | angled        |
| Material                            | PUR           |
| No. of poles                        | 4             |
| Degree of protection (EN IEC 60529) | IP20          |
| Commercial data                     |               |
| ECLASS-6.0                          | 27061801      |
| ECLASS-6.1                          | 27060307      |
| ECLASS-7.0                          | 27060307      |
| ECLASS-8.0                          | 27060307      |
| ECLASS-9.0                          | 27060307      |
| ECLASS-10.1                         | 27060307      |
| ECLASS-11.1                         | 27060307      |
| ECLASS-12.0                         | 27060307      |
| ETIM-5.0                            | EC002599      |
| customs tariff number               | 85444210      |
| customs tariff number               | 85444210      |
| EAN                                 | 4048879508599 |
| EAN                                 | 4048879508599 |
| Packaging unit                      | 1             |

Packaging unit 1

#### Electrical data | Supply

Operating voltage DC max. 60 V  
Current operating per contact max. 1,5 A

#### Industrial communication

Transfer parameters CAT5, Class D (ISO/IEC 11801:2002), (EN 50173-1)  
Data transmission rate max. 100 MBit/s

#### Industrial communication | Ethernet functionality

duplex Full duplex

#### Device protection | Electrical

Pollution Degree 3  
Rated surge voltage 1 kV  
Material group (IEC 60664-1) I

#### Mechanical data

Contour for corrugated hose without

#### Mechanical data | Material data

Locking material PA

#### Environmental characteristics | Climatic

Operating temperature min. -25 °C  
Operating temperature max. 85 °C  
Additional condition temperature range depending on cable quality

#### Important installation notes

Note on strain relief Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.  
Note on bending radius **Attention:** Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.

#### Conformity

Product standard according to IEC 60603-7 (RJ45)

#### Installation | Cable

|                                   |                                                                |
|-----------------------------------|----------------------------------------------------------------|
| wire arrangement                  | white, yellow, blue, orange                                    |
| Cable identification              | 796                                                            |
| Jacket Color                      | green                                                          |
| Type of Certificate               | cURus                                                          |
| Amount stranding                  | 1                                                              |
| Stranding                         | 4 wires around Core filler twisted                             |
| Cable shielding (type)            | copper braid, tinned                                           |
| Cable shielding (coverage)        | 85 %                                                           |
| Banding                           | Fleece, Foil                                                   |
| Filler                            | yes                                                            |
| wire arrangement                  | white, yellow, blue, orange                                    |
| Cable weight                      | 69,3 g/m                                                       |
| Material jacket                   | PUR                                                            |
| Shore hardness jacket             | 89 Shore A                                                     |
| Freedom from ingredients (jacket) | lead-free, cadmium-free, CFC-free, halogen-free, silicone-free |
| Outer-diameter (jacket)           | 6,7 mm                                                         |
| Tolerance outer diameter (sheath) | ± 5 %                                                          |
| Material inner jacket             | FRNC                                                           |
| Color (inner jacket)              | natural                                                        |
| Material wire insulation          | PE                                                             |
| Amount wires                      | 4                                                              |
| Outer diameter insulation         | 1,4 mm                                                         |

|                                                   |                                                      |
|---------------------------------------------------|------------------------------------------------------|
| Outer diameter tolerance core insulation          | ± 5 %                                                |
| Shore hardness wire insulation                    | 65 Shore D                                           |
| Ingredient freeness wire insulation               | lead-free, CFC-free, halogen-free                    |
| Amount strands (wire)                             | 7                                                    |
| Diameter of single wires                          | 22 AWG                                               |
| Conductor crosssection (wire)                     | 22 AWG                                               |
| Material conductor wire                           | Stranded copper wire, bare                           |
| Nominal voltage AC max.                           | 300 V                                                |
| Current load capacity (standard)                  | to DIN VDE 0298-4                                    |
| Current load capacity min. wire                   | 4,8 A                                                |
| Characteristic impedance                          | 100 Ω ± 15 % @ 100 MHz                               |
| Electrical resistance line constant wire          | 55 Ω/km @ 20 °C                                      |
| AC withstand voltage (wire - wire)                | 2 kV @ 60 s                                          |
| Electrical capacity line constant (wire - wire)   | 50000 pF/km                                          |
| Power frequency withstand voltage (wire - jacket) | 2 kV @ 60 s                                          |
| AC withstand voltage (wire - shield)              | 2 kV @ 60 s                                          |
| Isolation resistance                              | 5000 MΩ × km                                         |
| Min. operating temperature (static)               | -40 °C                                               |
| Max. operating temperature (fixed)                | 80 °C                                                |
| Operating temperature min. (dynamic)              | -30 °C                                               |
| Operating temperature max. (dynamic)              | 70 °C                                                |
| Flame resistance                                  | IEC 60332-2-2   UL 1581 § 1090   UL 1581 § 1100 FT2  |
| chemical resistance                               | Good, application-related testing                    |
| Gasoline resistance                               | Good, application-related testing                    |
| Oil resistance                                    | DIN EN 60811-404   Good, application-related testing |
| Bending radius (fixed)                            | 5 x Outer diameter                                   |
| Bending radius (dynamic)                          | 12 x Outer diameter                                  |
| No. of bending cycles (C-track)                   | 3 Mio. @ 25 °C                                       |
| Traversing distance (C-track)                     | 5 m @ 25 °C                                          |
| Travel speed (C-track)                            | 3,3 m/s @ 25 °C                                      |
| No. of torsion cycles                             | 1 Mio. 25 °C                                         |
| Torsion stress                                    | ± 180 °/m                                            |