

M12 female 0° A-cod. screw terminal F&B Pro4-pol., 0,25 - 1,0mm², 3,5 - 6mm

Art.No.: 7024-12901-0000000

Weight: 0.041

Country of origin: PL

Model designation: MSBL0-T



M12 F&B Pro

Female straight


4-pole

Screw terminals

The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)**Illustration**

Product may differ from Image

**Header**

Material short text

MSBL0-T

Side 1

Family construction form	M12
Degree of protection (EN IEC 60529)	IP67, IP69K, IP68, IP65
Commercial data	
URL Webshop	https://shop.murrelektronik.com/7024-12901-0000000
GTIN	4048879804608
ECLASS-6.0	27279221
ECLASS-6.1	27260702
ECLASS-7.0	27440102
ECLASS-7.1	27440102
ECLASS-8.0	27440102
ECLASS-8.1	27440102
ECLASS-9.0	27440116
ECLASS-9.1	27440106
ECLASS-10.0.1	27440106
ECLASS-10.1	27440102
ECLASS-11.0	27440106
ECLASS-11.1	27440102
ECLASS-12.0	27440116
ECLASS-13.0	27440106
ECLASS-14.0	27440106
ETIM-5.0	EC002635
ETIM-6.0	EC002635
ETIM-7.0	EC002635
ETIM-8.0	EC002635
customs tariff number	85366990
EAN	4048879804608
Packaging unit	1
Electrical data Supply	
Operating voltage AC max.	250 V
Operating voltage DC max.	300 V
Current operating per contact max.	4 A
Installation	
Connection cross section min.	0.25 mm²
Connection cross section max.	1 mm²
Installation Connection	
Tightening torque	0.6 Nm
Mounting set	M12 x 1
Width across flats	SW19
Device protection Electrical	
Additional condition protection degree	inserted, screwed
Mechanical data Material data	
Material housing	PA
Locking material	Stainless steel
Material gasket	EPDM
Mechanical data Mounting data	
Mounting method	Schraubgewinde
Clamping range min.	3.5 mm
Clamping range max.	6 mm
Environmental characteristics Climatic	
Operating temperature min.	-25 °C
Operating temperature max.	100 °C

Important installation notes

Note on bending radius	Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.
Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.