

Cable drum Ø 500mm

PUR 3x0.34 shielded gy UL/CSA 500m

Art.No.: 7000-C0505-3190000  
Weight: 25.003  
Country of origin: DE  
Model designation: 500m Kabel 50080922(319)gesch.Kabeltromm


PUR (UL/CSA)  
3× 0.34 mm², grey  
shielded  
Cable drum (500 m)

Link to Product

Illustration



Product may differ from Image



Commercial data

|                       |               |
|-----------------------|---------------|
| ECLASS-6.0            | 27062011      |
| ECLASS-6.1            | 27061801      |
| ECLASS-7.0            | 27061801      |
| ECLASS-8.0            | 27061801      |
| ECLASS-9.0            | 27061801      |
| ECLASS-10.1           | 27061801      |
| ECLASS-11.1           | 27061801      |
| ECLASS-12.0           | 27061801      |
| ETIM-5.0              | EC001855      |
| customs tariff number | 85444995      |
| customs tariff number | 85444995      |
| EAN                   | 4048879560740 |
| EAN                   | 4048879560740 |
| Packaging unit        | 1             |
| Packaging unit        | 1             |

Installation | Cable

|                      |                 |
|----------------------|-----------------|
| Cable identification | 319             |
| Jacket Color         | gray            |
| Type of Certificate  | cURus           |
| Amount stranding     | 1               |
| Stranding            | 3 wires twisted |

|                                                   |                                                                |
|---------------------------------------------------|----------------------------------------------------------------|
| Stranding factor min.                             | 55 mm                                                          |
| Stranding factor max.                             | 55 mm                                                          |
| Cable shielding (type)                            | copper braid, tinned                                           |
| Cable shielding (coverage)                        | 85 %                                                           |
| Banding                                           | Fleece, Foil                                                   |
| wire arrangement                                  | brown, black, blue                                             |
| Cable weight                                      | 55 g/m                                                         |
| Material jacket                                   | PUR                                                            |
| Shore hardness jacket                             | 85 ± 3 Shore A                                                 |
| Freedom from ingredients (jacket)                 | lead-free, cadmium-free, CFC-free, halogen-free                |
| Outer-diameter (jacket)                           | 5,9 mm                                                         |
| Tolerance outer diameter (sheath)                 | ± 5 %                                                          |
| Material wire insulation                          | PP                                                             |
| Amount wires                                      | 3                                                              |
| Outer diameter insulation                         | 1,55 mm                                                        |
| Outer diameter tolerance core insulation          | ± 5 %                                                          |
| Shore hardness wire insulation                    | 72 ± 3 Shore D                                                 |
| Ingredient freeness wire insulation               | lead-free, cadmium-free, CFC-free, halogen-free, silicone-free |
| Amount strands (wire)                             | 42                                                             |
| Diameter of single wires                          | 0,1 mm                                                         |
| Conductor crosssection (wire)                     | 0,34 mm <sup>2</sup>                                           |
| Material conductor wire                           | Stranded copper wire, bare                                     |
| Conductor type (wire)                             | strand class 6                                                 |
| Nominal voltage AC max.                           | 300 V                                                          |
| Current load capacity (standard)                  | to DIN VDE 0298-4                                              |
| Current load capacity min. wire                   | 6 A                                                            |
| Electrical resistance line constant wire          | 53 Ω/km @ 20 °C                                                |
| AC withstand voltage (wire - wire)                | 2 kV @ 60 s                                                    |
| Power frequency withstand voltage (wire - jacket) | 2 kV @ 60 s                                                    |
| AC withstand voltage (wire - shield)              | 2 kV @ 60 s                                                    |
| Min. operating temperature (static)               | -40 °C                                                         |
| Max. operating temperature (fixed)                | 80 °C                                                          |
| Operating temperature min. (dynamic)              | -20 °C                                                         |
| Operating temperature max. (dynamic)              | 80 °C                                                          |
| Flame resistance                                  | IEC 60332-2-2   UL 1581 § 1090   UL 1581 § 1100 FT2            |
| chemical resistance                               | Good, application-related testing                              |
| Gasoline resistance                               | Good, application-related testing                              |
| Oil resistance                                    | Good, application-related testing   DIN EN 60811-404           |
| Bending radius (dynamic)                          | 10 x Outer diameter                                            |