

**M12 male 0° Lite / MSUD valve plug A-18mm**

PUR 3x0.75 bk UL/CSA 0.3m

Art.No.: 7005-40881-6260030

Weight: 0.062

Country of origin: CZ

Model designation: MSKL3-A-W626\_0.3-YF-S02-S05

Form A (18 mm) – M12, male straight

3-pole

24 V AC  $\pm 20\%$  / DC  $\pm 25\%$ 

LED and suppression




Bridged PE




7005 - plastic hexagonal screw (M12 Lite)

Further cable lengths on request.

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

**[Link to Product](#)****Illustration**



Product may differ from Image



|                                           |          |
|-------------------------------------------|----------|
| Cable length                              | 0,3 m    |
| Side 1                                    |          |
| Tightening torque                         | 0,4 Nm   |
| Family construction form                  | M12      |
| Thread                                    | M3       |
| suitable for corrugated tube (internal Ø) | 10 mm    |
| Material                                  | PBT      |
| Width across flats                        | SW13     |
| Degree of protection (EN IEC 60529)       | IP67     |
| Side 2                                    |          |
| Tightening torque                         | 0,6 Nm   |
| Thread                                    | M12 x 1  |
| Degree of protection (EN IEC 60529)       | IP67     |
| Commercial data                           |          |
| ECLASS-6.0                                | 27279218 |
| ECLASS-7.0                                | 27279218 |
| ECLASS-8.0                                | 27279218 |

|                       |               |
|-----------------------|---------------|
| ECLASS-9.0            | 27060311      |
| ECLASS-10.1           | 27060312      |
| ECLASS-11.1           | 27060312      |
| ECLASS-12.0           | 27060312      |
| ETIM-5.0              | EC001855      |
| customs tariff number | 85444290      |
| customs tariff number | 85444290      |
| EAN                   | 4048879603089 |
| EAN                   | 4048879603089 |
| Packaging unit        | 1             |
| Packaging unit        | 1             |

#### Electrical data

|                          |       |
|--------------------------|-------|
| Drop-out delay time max. | 20 ms |
|--------------------------|-------|

#### Electrical data | Supply

|                                    |        |
|------------------------------------|--------|
| Operating voltage AC               | 24 V   |
| Operating voltage AC min.          | 19,2 V |
| Operating voltage AC max.          | 28,8 V |
| Operating voltage DC               | 24 V   |
| Operating voltage DC min.          | 18 V   |
| Operating voltage DC max.          | 30 V   |
| Cut-off peak voltage max.          | 55 V   |
| Current operating per contact max. | 4 A    |
| Current consumption max.           | 15 mA  |

#### Diagnostics

|                       |        |
|-----------------------|--------|
| Status indication LED | yellow |
|-----------------------|--------|

#### Device protection | Electrical

|                                        |                   |
|----------------------------------------|-------------------|
| Additional condition protection degree | inserted, screwed |
| Pollution Degree                       | 3                 |
| Rated surge voltage                    | 0,8 kV            |
| Material group (IEC 60664-1)           | I                 |

#### Mechanical data | Material data

|                  |         |
|------------------|---------|
| Material housing | Plastic |
| Color housing    | black   |
| Material gasket  | Silicon |
| Material jacket  | PUR     |
| Locking material | PA      |

#### Environmental characteristics | Climatic

|                                        |                            |
|----------------------------------------|----------------------------|
| Operating temperature min.             | -25 °C                     |
| Operating temperature max.             | 85 °C                      |
| Additional condition temperature range | depending on cable quality |

#### Important installation notes

|                        |                                                                                                                                                       |
|------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|
| Note on strain relief  | Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.                                                   |
| Note on bending radius | <b>Attention:</b> Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces. |

#### Installation | Cable

|                                   |                                |
|-----------------------------------|--------------------------------|
| wire arrangement                  | black 1, black 2, green-yellow |
| Cable identification              | 626                            |
| Cable Type                        | 2                              |
| Printing color of wire insulation | white (isolation black)        |
| Jacket Color                      | black                          |
| Type of Certificate               | cURus                          |

|                                                   |                                                      |
|---------------------------------------------------|------------------------------------------------------|
| Amount stranding                                  | 1                                                    |
| Stranding                                         | 3 wires twisted                                      |
| wire arrangement                                  | black 1, black 2, green-yellow                       |
| Cable weight                                      | 55,33 g/m                                            |
| Material jacket                                   | PUR                                                  |
| Shore hardness jacket                             | 85 ± 5 Shore A                                       |
| Freedom from ingredients (jacket)                 | lead-free, cadmium-free, CFC-free, silicone-free     |
| Outer-diameter (jacket)                           | 5,9 mm                                               |
| Tolerance outer diameter (sheath)                 | ± 5 %                                                |
| Material inner jacket                             | PVC                                                  |
| Color (inner jacket)                              | black                                                |
| Material wire insulation                          | PVC                                                  |
| Amount wires                                      | 3                                                    |
| Outer diameter insulation                         | 1,8 mm                                               |
| Outer diameter tolerance core insulation          | ± 5 %                                                |
| Shore hardness wire insulation                    | 43 ± 5 Shore D                                       |
| Material properties wire insulation               | good machinability                                   |
| Ingredient freeness wire insulation               | lead-free, cadmium-free, CFC-free, silicone-free     |
| Printing color of wire insulation                 | white (isolation black)                              |
| Amount strands (wire)                             | 42                                                   |
| Diameter of single wires                          | 0,15 mm                                              |
| Conductor crosssection (wire)                     | 0,75 mm <sup>2</sup>                                 |
| Material conductor wire                           | Stranded copper wire, bare                           |
| Conductor type (wire)                             | strand class 6                                       |
| Nominal voltage AC max.                           | 300 V                                                |
| Current load capacity (standard)                  | to DIN VDE 0298-4                                    |
| Current load capacity min. wire                   | 12 A                                                 |
| Electrical resistance line constant wire          | 26 Ω/km @ 20 °C                                      |
| AC withstand voltage (wire - wire)                | 2 kV @ 60 s                                          |
| Power frequency withstand voltage (wire - jacket) | 2 kV @ 60 s                                          |
| Min. operating temperature (static)               | -30 °C                                               |
| Max. operating temperature (fixed)                | 80 °C                                                |
| Operating temperature min. (dynamic)              | -5 °C                                                |
| Operating temperature max. (dynamic)              | 80 °C                                                |
| UV resistance                                     | DIN EN ISO 4892-2 A                                  |
| Flame resistance                                  | UL 1581 § 1090   IEC 60332-2-2   UL 1581 § 1100 FT2  |
| chemical resistance                               | Good, application-related testing                    |
| Gasoline resistance                               | Good, application-related testing                    |
| Oil resistance                                    | Good, application-related testing   DIN EN 60811-404 |
| Bending radius (fixed)                            | 10 x Outer diameter                                  |
| Bending radius (dynamic)                          | 15 x Outer diameter                                  |
| No. of bending cycles (C-track)                   | 2 Mio. @ 25 °C                                       |
| Traversing distance (C-track)                     | 5 m @ 25 °C                                          |
| Travel speed (C-track)                            | 3,3 m/s @ 25 °C                                      |