

**M12 female 0° A-cod. with cable shielded F&B**

PVC 5x0.34 shielded gy UL/CSA 1.5m

Art.No.: 7014-13221-2030150

Weight: 0.118

Country of origin: CZ

Model designation: MSBL0-U203\_1.5-ZS-S14

Plug Connectors for Food &amp; Beverage

Female straight

M12, 5-pole





shielded


Profile gasket

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

Further cable lengths on request.

[Link to Product](#)**Illustration**



Product may differ from Image



|                                     |                                |
|-------------------------------------|--------------------------------|
| Cable length                        | 1,5 m                          |
| Side 1                              |                                |
| Tightening torque                   | 0,6 Nm                         |
| Mounting method                     | inserted, screwed              |
| Coating contact                     | gold plated                    |
| Family construction form            | M12                            |
| Thread                              | M12 x 1                        |
| Cable outlet                        | straight                       |
| Coding                              | A                              |
| Material contact                    | Copper alloy                   |
| No. of poles                        | 5                              |
| Width across flats                  | SW14                           |
| Degree of protection (EN IEC 60529) | IP65, IP66K, IP67, IP68, IP69K |
| Side 2                              |                                |
| Stripping length (jacket)           | 20 mm                          |
| Family construction form            | free cable end                 |
| Commercial data                     |                                |
| ECLASS-6.0                          | 27279221                       |
| ECLASS-6.1                          | 27279218                       |
| ECLASS-7.0                          | 27279218                       |
| ECLASS-8.0                          | 27279218                       |
| ECLASS-9.0                          | 27060311                       |
| ECLASS-10.1                         | 27060311                       |
| ECLASS-11.1                         | 27060311                       |
| ECLASS-12.0                         | 27060311                       |
| ETIM-5.0                            | EC001855                       |
| customs tariff number               | 85444290                       |
| customs tariff number               | 85444290                       |
| EAN                                 | 4048879772983                  |
| EAN                                 | 4048879772983                  |
| Packaging unit                      | 1                              |
| Packaging unit                      | 1                              |
| Electrical data   Supply            |                                |

|                                                 |                                                                                                                                                       |
|-------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|
| Operating voltage AC max.                       | 60 V                                                                                                                                                  |
| Operating voltage DC max.                       | 60 V                                                                                                                                                  |
| Current operating per contact max.              | 4 A                                                                                                                                                   |
| <b>Diagnostics</b>                              |                                                                                                                                                       |
| Status indication LED                           | no                                                                                                                                                    |
| <b>Installation   Connection</b>                |                                                                                                                                                       |
| Stripping length (jacket)                       | 20 mm                                                                                                                                                 |
| Gender                                          | female                                                                                                                                                |
| <b>Device protection   Electrical</b>           |                                                                                                                                                       |
| Degree of protection (EN IEC 60529)             | IP65, IP67, IP68, IP66K, IP69K                                                                                                                        |
| Additional condition protection degree          | inserted, screwed                                                                                                                                     |
| Pollution Degree                                | 3                                                                                                                                                     |
| Rated surge voltage                             | 1,5 kV                                                                                                                                                |
| Material group (IEC 60664-1)                    | I                                                                                                                                                     |
| <b>Mechanical data</b>                          |                                                                                                                                                       |
| Contour for corrugated hose                     | without                                                                                                                                               |
| <b>Mechanical data   Material data</b>          |                                                                                                                                                       |
| Locking material                                | Stainless steel 1.4404 (V4A)                                                                                                                          |
| <b>Mechanical data   Mounting data</b>          |                                                                                                                                                       |
| Mounting method                                 | inserted, screwed, Shaking protection                                                                                                                 |
| <b>Environmental characteristics   Climatic</b> |                                                                                                                                                       |
| Operating temperature min.                      | -25 °C                                                                                                                                                |
| Operating temperature max.                      | 85 °C                                                                                                                                                 |
| Additional condition temperature range          | depending on cable quality                                                                                                                            |
| <b>Important installation notes</b>             |                                                                                                                                                       |
| Note on strain relief                           | Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.                                                   |
| Note on bending radius                          | <b>Attention:</b> Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces. |
| <b>Conformity</b>                               |                                                                                                                                                       |
| Product standard                                | DIN EN 61076-2-101 (M12)                                                                                                                              |
| <b>Installation   Cable</b>                     |                                                                                                                                                       |
| wire arrangement                                | brown, black, blue, white, gray                                                                                                                       |
| Cable identification                            | 203                                                                                                                                                   |
| Cable Type                                      | 1                                                                                                                                                     |
| Jacket Color                                    | gray                                                                                                                                                  |
| Type of Certificate                             | cURus                                                                                                                                                 |
| Amount stranding                                | 1                                                                                                                                                     |
| Stranding                                       | 5 wires around Core filler twisted                                                                                                                    |
| Cable shielding (type)                          | copper braid, tinned                                                                                                                                  |
| Cable shielding (coverage)                      | 80 %                                                                                                                                                  |
| Banding                                         | Fleece, Foil                                                                                                                                          |
| Filler                                          | yes                                                                                                                                                   |
| wire arrangement                                | brown, black, blue, white, gray                                                                                                                       |
| Cable weight                                    | 68,2 g/m                                                                                                                                              |
| Material jacket                                 | PVC                                                                                                                                                   |
| Shore hardness jacket                           | 85 ± 5 Shore A                                                                                                                                        |
| Freedom from ingredients (jacket)               | lead-free, cadmium-free, CFC-free, silicone-free                                                                                                      |
| Outer-diameter (jacket)                         | 5,6 mm                                                                                                                                                |
| Tolerance outer diameter (sheath)               | ± 5 %                                                                                                                                                 |
| Material wire insulation                        | PVC                                                                                                                                                   |

|                                                   |                                                      |
|---------------------------------------------------|------------------------------------------------------|
| Amount wires                                      | 5                                                    |
| Outer diameter insulation                         | 1,25 mm                                              |
| Outer diameter tolerance core insulation          | ± 5 %                                                |
| Shore hardness wire insulation                    | 45 ± 5 Shore D                                       |
| Material properties wire insulation               | good machinability                                   |
| Ingredient freeness wire insulation               | lead-free, cadmium-free, CFC-free, silicone-free     |
| Amount strands (wire)                             | 19                                                   |
| Diameter of single wires                          | 0,15 mm                                              |
| Conductor crosssection (wire)                     | 0,34 mm <sup>2</sup>                                 |
| Material conductor wire                           | Stranded copper wire, bare                           |
| Conductor type (wire)                             | Strand class 5                                       |
| Nominal voltage AC max.                           | 300 V                                                |
| Current load capacity (standard)                  | to DIN VDE 0298-4                                    |
| Current load capacity min. wire                   | 4,5 A                                                |
| Electrical resistance line constant wire          | 57 Ω/km @ 20 °C                                      |
| AC withstand voltage (wire - wire)                | 2 kV @ 60 s                                          |
| Power frequency withstand voltage (wire - jacket) | 2 kV @ 60 s                                          |
| AC withstand voltage (wire - shield)              | 2 kV @ 60 s                                          |
| Min. operating temperature (static)               | -30 °C                                               |
| Max. operating temperature (fixed)                | 80 °C                                                |
| Operating temperature min. (dynamic)              | -5 °C                                                |
| Operating temperature max. (dynamic)              | 80 °C                                                |
| Flame resistance                                  | UL 1581 § 1090   IEC 60332-2-2   UL 1581 § 1100 FT2  |
| chemical resistance                               | Good, application-related testing                    |
| Gasoline resistance                               | Good, application-related testing                    |
| Oil resistance                                    | DIN EN 60811-404   Good, application-related testing |
| Bending radius (fixed)                            | 10 x Outer diameter                                  |
| Bending radius (dynamic)                          | 15 x Outer diameter                                  |