

MB DIODE



IN: 24VDC/2x20ADC OUT: 24V/20-40ADC

Art.No.: 85396
Weight: 0.326
Country of origin: CZ
Model designation: MB Diode

INPUT: 24 V DC (SELV/PELV)
OUTPUT: max. 2x 20/1x 40 A

Link to Product

Illustration



Product may differ from Image



Header	
Material short text	MB Diode
Commercial data	
URL Webshop	https://shop.murrelektronik.com/85396
GTIN	4048879079884

ECLASS-6.0	27049002
ECLASS-6.1	27049002
ECLASS-7.0	27049002
ECLASS-7.1	27049002
ECLASS-8.0	27049002
ECLASS-8.1	27049002
ECLASS-9.0	27040701
ECLASS-9.1	27040701
ECLASS-10.0.1	27040701
ECLASS-10.1	27040701
ECLASS-11.0	27040701
ECLASS-11.1	27040701
ECLASS-12.0	27040701
ECLASS-13.0	27040701
ECLASS-14.0	27040701
ETIM-5.0	EC002540
ETIM-6.0	EC002540
ETIM-7.0	EC002540
ETIM-8.0	EC002540
customs tariff number	85411000
EAN	4048879079884
Packaging unit	1

Electrical data | Supply

Total current max.	40 A
--------------------	------

Electrical data | Input

Input voltage DC	24 V
Input voltage DC min.	21 V
Input voltage DC max.	30 V
Current input AC	40 A
Total current bridge set max.	40 A
Efficiency	97 %

Electrical data | Output

Output voltage adjustable	yes
Output voltage DC	24 V
Output voltage DC min.	21 V
Output voltage DC max.	30 V
Output current	20 A
Output current (UL)	40 A
Overload current	at 20 A +50% for 4 s

Diagnostics

Alarm contact	yes
Alarm contact potential free	yes
Alarm contact message type	per channel

Installation | Connection

Connection	Spring clamp terminals FK
------------	---------------------------

Device protection | Electrical

Invers-polarity protection	yes
----------------------------	-----

Mechanical data | Mounting data

Mounting method	geschnappt
Suitable for mounting type	Mounting rail TH35, (EN 60715)

Environmental characteristics | Electromagnetic compatibility

Emission standard for equipment in residential environments (IEC 61000-6-3) compliant

Immunity standard for industrial environments (IEC 61000-6-2) compliant

Environmental characteristics | Climatic

Operating temperature min.	-25 °C
Operating temperature max.	55 °C
Storage temperature min.	-25 °C
Storage temperature max.	85 °C
Relative humidity min. (operation)	5 %
Relative humidity max. (operation)	95 % no condensation