


# **Features**

- Bright indication of sensor power and output status
  Two colors: Green indicates the power is on and amber indicates an active input
- Meets IP66, IP67, IP68
- Models available for PNP or NPN outputs



### Models

4-Pin Single-Ended M12 Female Lighted Cordsets					
Model	Length	Input Type	Style	Dimensions	Pinout (Female)
MQDC-406-GYP	2 m (6.5 ft)	PNP	Straight	44 Typ.  M12 x 1  Ø 14.5	1 = Brown 2 = White 3 = Blue 4 = Black 5 = Not used Green LED indicates the power is on and amber LED indicates an active input
MQDC-406-GYN		NPN			
MQDC-415-GYP	5 m (16.5 ft)	PNP			
MQDC-415-GYN		NPN			
MQDC-430-GYP	9 m (29.5 ft)	PNP			
MQDC-430-GYN		NPN			
MQDC-406-GYPRA	2 m (6.5 ft)	PNP	Right-Angle	32 Typ. [1.26] 30 Typ. [1.18] M12 x 1	
MQDC-406-GYNRA		NPN			
MQDC-415-GYPRA	5 m (16.5 ft)	PNP			
MQDC-415-GYNRA		NPN			
MQDC-430-GYPRA	9 m (29.5 ft)	PNP			
MQDC-430-GYNRA		NPN			

5-Pin Single-Ended M12 Female Lighted Cordsets					
Model	Length	Input Type	Style	Dimensions	Pinout (Female)
MQDC-506-GYP	2 m (6.5 ft)	PNP	Straight	44 Typ. M12 x 1 Ø 14.5	1 = Brown 2 = White 3 = Blue 4 = Black 5 = Gray  Green LED indicates the power is on and amber LED indicates an active input
MQDC-506-GYN		NPN			
MQDC-515-GYP	5 m (16.5 ft)	PNP			
MQDC-515-GYN		NPN			
MQDC-530-GYP	9 m (29.5 ft)	PNP			
MQDC-530-GYN		NPN			
MQDC-506-GYPRA	2 m (6.5 ft)	PNP	Right-Angle	32 Typ. [1.26"] 30 Typ. [1.18"] 414.5 [0.57"]	
MQDC-506-GYNRA		NPN			
MQDC-515-GYPRA	5 m (16.5 ft)	PNP			
MQDC-515-GYNRA		NPN			
MQDC-530-GYPRA	9 m (29.5 ft)	PNP			
MQDC-530-GYNRA		NPN			

# Wiring Diagrams

Female	Pin	Wire Color	Description
1 00003	1	Brown	10 V DC to 30 V DC; the green Power LED is on (color 1)
	2	White	Pass through
	3	Blue	DC common
	4	Black	Input from sensor; the amber output LED (color 2) overrides the green Power LED when it is active
	5 0	Gray	Not used for 4-pin models
			Pass through for 5-pin models



### **Specifications**

#### Supply Voltage

10 V DC to 30 V DC at 15 mA maximum

#### **Supply Protection Circuitry**

Protected against reverse polarity and transient voltages

#### Leakage Current Immunity

400 µA

#### Indicators

Two colors

Color 2 overrides Color 1

#### **Environmental Rating**

IP67, IP68

NEMA 1, UL Type 1

#### **Operating Conditions**

#### Temperature:

Maximum current of 1.0 A: -40 °C to +60 °C (-40 °F to +140 °F)

Maximum current of 2.0 A: -40 °C to +55 °C (-40 °F to

Maximum current of 4.0 A: -40 °C to +45 °C (-40 °F to +113 °F)

90% at +50 °C maximum relative humidity (non-condensing)

### Storage Temperature: -40 °C to +70 °C (-40 °F to +158 °F)

#### Connections

Integral 5-pin or 4-pin M12 female quick disconnect connector

#### Construction

Coupling Material: Nickel-plated brass Connector Body: PVC translucent white

Cable Material: PVC

#### Vibration and Mechanical Shock

Meets IEC 60068-2-6 requirements (Vibration: 10 Hz to 55 Hz, 1.0 mm amplitude, 5 minutes sweep, 30 minutes dwell) Meets IEC 60068-2-27 requirements (Shock: 30G 11 ms

duration, half sine wave)

#### Certifications



Banner Engineering BV Park Lane, Culliganlaan 2F bus 3 1831 Diegem, BELGIUM



Turck Banner LTD Blenheim House Blenheim Court Wickford, Essex SS11 8YT GREAT BRITAIN



#### Required Overcurrent Protection



WARNING: Electrical connections must be made by qualified personnel in accordance with local and national electrical codes and regulations.

Overcurrent protection is required to be provided by end product application per the supplied table.

Overcurrent protection may be provided with external fusing or via Current Limiting, Class 2 Power Supply.


Supply wiring leads < 24 AWG shall not be spliced.

For additional product support, go to www.bannerengineering.com.

Supply Wiring (AWG)	Required Overcurrent Protection (A)	Supply Wiring (AWG)	Required Overcurrent Protection (A)
20	5.0	26	1.0
22	3.0	28	0.8
24	1.0	30	0.5

### **Dimensions**

All measurements are listed in millimeters [inches], unless noted otherwise. The measurements provided are subject to change.



## Banner Engineering Corp Limited Warranty

Banner Engineering Corp. warrants its products to be free from defects in material and workmanship for one year following the date of shipment. Banner Engineering Corp. will repair or replace, free of charge, any product of its manufacture which, at the time it is returned to the factory, is found to have been defective during the warranty period. This warranty does not cover damage or liability for misuse, abuse, or the improper application or installation of the Banner product.

THIS LIMITED WARRANTY IS EXCLUSIVE AND IN LIEU OF ALL OTHER WARRANTIES WHETHER EXPRESS OR IMPLIED (INCLUDING, WITHOUT LIMITATION, ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE), AND WHETHER ARISING UNDER COURSE OF PERFORMANCE, COURSE OF DEALING OR TRADE USAGE.

This Warranty is exclusive and limited to repair or, at the discretion of Banner Engineering Corp., replacement. IN NO EVENT SHALL BANNER ENGINEERING CORP. BE LIABLE TO BUYER OR ANY OTHER PERSON OR ENTITY FOR ANY EXTRA COSTS, EXPENSES, LOSSES, LOSSES, LOSS OF PROFITS, OR ANY INCIDENTAL, CONSEQUENTIAL OR SPECIAL

## DAMAGES RESULTING FROM ANY PRODUCT DEFECT OR FROM THE USE OR INABILITY TO USE THE PRODUCT, WHETHER ARISING IN CONTRACT OR WARRANTY, STATUTE, TORT, STRICT LIABILITY, NEGLIGENCE, OR OTHERWISE.

Banner Engineering Corp. reserves the right to change, modify or improve the design of the product without assuming any obligations or liabilities relating to any product previously manufactured by Banner Engineering Corp. Any misuse, abuse, or improper application or installation of this product or use of the product for personal protection applications when the product is identified as not intended for such purposes will void the product warranty. Any modifications to this product without prior express approval by Banner Engineering Corp will void the product warranties. All specifications published in this document are subject to change; Banner reserves the right to modify product specifications or update documentation at any time. Specifications and product information in English supersede that which is provided in any other language. For the most recent version of any documentation, refer to:

www.bannerengineering.com.

For patent information, see www.bannerengineering.com/patents.