
Phase Monitor Relays (3-Phase Monitors) provide cost-effective protection against premature equipment failure caused by voltage faults on 3-Phase systems (Wye or Delta). The SLU Series multi-mode phase monitoring relay, was designed for the convenience of electrician's, maintenance managers and engineers. A single SLU Phase Monitoring Relay can be easily adjusted for the voltage, imbalance percentage and time delay requirements to protect against unbalanced voltages or single phasing regardless of any regenerative voltages.

Both **DELTA** and **WYE** systems may be monitored. In Wye systems, connections to neutral are NOT required. The SLU-100 Series is UL Listed under UL File Number E55826.

NOTE: Not recommended for generator or variable frequency drive applications. Call technical support for application assistance.






Universal Phase Monitor

SPECIFICATIONS

3PECIFICA	4110N2		
AUTO	Frequency	Nominal Line-to-Line	Adjustable
RANGING		Voltages	Range
SCALES	60Hz	208, 220, 240, 380,	200-250
		415, 440, 460, 480	360-500
	50Hz	208, 220, 240	200-250
		346, 380, 415	330-430
VOLTAGE BAND	Drop-out	±10% of Range Setti	
	Pick-up	±7% of Range Settin	g (Under/Over)
MAXIMUM VOLTAGE	550 VAC (Line-to-Line)		
PHASE SEQUENCE	ABC (Will Not Operate On CBA Sequence)		
POWER REQUIRED	90VA Max.		
PHASE	2% to 10%	, Adjustable Drop-out	
UNBALANCE	Hysteresis	10% of Setting	
PHASE SHIFT	13° Drop-out, 12° Pick-up (Ø-Loss)		
FREQUENCY	50/60 Hz		
SHIFT	Drop-out	± 4%	
	Pick up	± 3%	
RESET	Automatic or Manual Mode		
RELAY OUTPUT	SPDT, 10A @ 240VAC Resistive, 1/2 HP @240VAC		
INDICATORS		Flashing	Continuous
	Normal	Fault Delay Active	Relay
	(Green LED)		Energized
	Fault	Restart Delay Active	Relay
	(Red LED)		De-energized
RESPONSE	Power Up	2.5 SEC Minimum	
	Fault Delay	.1 to 25 SEC., Adjusta	
	Severe Faul	,	Unbalance or
		Phase Reversal)	
	Restart	0.5 to 300 S, Adjustal	ole (Auto Rese
TEMPERATURE	Operate	` ,	
RATINGS	Storage		
REPEAT ACCURACY	1% @ Fixed Condition		
TERMINALS (DIN)	Slotted Screw Terminal Clamps, 12AWG Max.		
ENCLOSURE	Style "A"	LEXAN® Dust Cover	
	DIN	35mm DIN Rail, 14 Te	rm
		Polycarbonate Housin	g
WEIGHT	0.35 to 0.5	lbs.	

ORDERING INFORMATION

MODEL NUMBER	DESCRIPTION	
SLU-100-ASA	Universal Phase Monitor	
SLU-100-ASD	Din Rail Mount Universal Phase Monitor	



Socket Unit DIMENSIONS (INCHES) Socket Unit 2.38' 0A 0B 0C 2.38' 03.4 5 60 2.95 1.77 DIN Mount Unit 4.33