



# EZConnect™ Cable Harness

## Fast Turnaround Customizations



EZConnect Cable Harnesses are designed to be compatible with a variety of Airgain's external antennas featuring the versatile EZConnect configuration. Customizations are available as *made-to-order* from a North American factory for quick delivery right to your door.

### KEY FEATURES

- Seamless connection to MULTIMAX™ 5G, RECON13™, RECON5™, and M2MAX® antennas with EZConnect configuration as well as the whip base adapter
- Up to 14 cables supporting combinations of cellular, Wi-Fi/Bluetooth, whip, and GNSS technologies
- Made with low-loss, flexible LMR-195 outdoor-rated coax cable

### ADVANTAGES

- Includes mesh around all cables and heat shrink labels on each side
- An assortment of connectors are available for connecting to virtually any vehicular router or modem
- One week lead time and no minimum order quantity for custom cable lengths and router side connectors

EZConnect Antenna with LMR-100 cables	EZConnect Cable Harness with LMR-195 cables
Cell Connectors: SMA Male	Cell Connectors: SMA Female
Wi-Fi Connectors: SMA Female	Wi-Fi Connectors: SMA Male
Whip Connector: FME Male	Whip Connector: FME Female
GNSS Connector: FME Female	GNSS Connector: FME Male

The EZConnect Antenna has one-foot cables with standard connectors for seamlessly connecting to the EZConnect Cable Harness.

For more Information:

[www.airgain.com](http://www.airgain.com) [sales@airgain.com](mailto:sales@airgain.com) + 1-855-AIRGAIN

Preliminary product information. Specifications are subject to change without notice.  
Copyright © 2025 All Rights Reserved. Registered Trademarks TM Airgain, Inc. Airgain, Lighthouse, and their associated logos are trademarks or registered trademarks of Airgain, Inc.  
Revised 07/24/25



# EZConnect™ Cable Harness

## Fast Turnaround Customizations

### EZConnect CABLE HARNESS PART NUMBER CONFIGURATION TABLE

Brand Code	-	Cell Elements	Wi-Fi Elements	Other	GNSS	-	Router Side Connectors							-	Cable Length (ft)		
							Cell	-	Wi-Fi	-	Other	-	GNSS				
CH for select SKUs or CCH for Custom Cable Harness		(optional)	(optional)	(optional)	(optional)	*Inquire to Airgain	(optional)							User Defined			
		C = 1 Element	W = 1 Element	P = Whip	G = GNSS		1 = SMA Male										
		C2 = 2 Elements	W2 = 2 Elements	2 = SMA Male RP													
		C3 = 3 Elements	W3 = 3 Elements	3 = SMA Female													
		C4 = 4 Elements	W4 = 4 Elements	4 = TNC Male													
		W5 = 5 Elements	5 = TNC Male RP														
		W6 = 6 Elements	6 = BNC Male														
		W7 = 7 Elements	7 = BNC Female														
		W8 = 8 Elements	8 = SMB Male														
		9 = SMB Female															
		A = Mini UHF Male															
		B = N-Type Male															
		C = FAKRA C (Signal Blue for GNSS)															
		D = FAKRA D (Claret Violet for Cell)															
		E = N-Type Female															
		F = QMA Male															
		G = QMA Female															
		H = FAKRA H (Pink)															
		I = FAKRA I (Beige for Wi-Fi)															
		Z = FAKRA Z (Water Blue for Bluetooth)															

For more Information:

[www.airgain.com](http://www.airgain.com) [sales@airgain.com](mailto:sales@airgain.com) + 1-855-AIRGAIN

Preliminary product information. Specifications are subject to change without notice.  
Copyright © 2025 All Rights Reserved. Registered Trademarks TM Airgain, Inc. Airgain, Lighthouse, and their associated logos are trademarks or registered trademarks of Airgain, Inc.

Revised 07/24/25